



FF-MED red lot design award winner 2012 MEGAPROGRESS

Product overview MEGAprogress

functional cabinet series redesign valid from 1.1.2015

Former serial product of Blanco Professional



MEGAPROGRESS - CONTENTS

Contents	ISO module base cabinet78
Stainless-steel table tops	ISO module high cabinet
Stainless-steel table top accessories 5	ISO module wall cabinet
Welded-in basin7	ISO module top-mounted cabinet86
Hospital drain	Module equipment87
Stainless-steel basin accessories 10	
Fittings and mixer taps12	STU high cabinet
Fitting and mixer tap accessories 14	Pass-through compartment system
Table top accessories – general	STU accessories
	Plinth
Base cabinet as per DIN standard 17	Cabinet shelf
Base cabinet – refrigeration unit	Shelf
Base cabinet with warming device	Light panels and accessories
Warming drawer	LED light panels and accessories 106
Base cabinet for drain35	Electronic lock and accessories 107
Base cabinet for ultrasound unit36	FF-click, accessories and partition wall 108
Gynaecology cabinet	Narcotics safe
Plaster bench system and accessories39	Accessories
	Refrigeration units115
High cabinet as per DIN standard42	Panels as per DIN and ISO standard,
Implant cabinet	powder-coated118
Endoscopy cabinet52	Panels as per DIN and ISO standard,
Catheter cabinet57	stainless steel119
Drug cabinet	Ladders for cabinets as per DIN and
Practice cabinet	ISO standard
High cabinet for refrigeration units62	Panels as per DIN and ISO standard121
Combination cabinet	Wall shelf
Warming drawer	
Wall cabinet as per DIN standard	

Top-mounted cabinet as per DIN standard . . 77

FF Co. Ltd.

Budapest - HQ Office

H-1101 Budapest, Kőbányai út 49.

Tel.: +36 1 4342 995

Fax: +36 1 4342 994

Mezőtúr - Factory

H-5400 Mezőtúr, Vásárhelyi Pál u. 2.

Tel.: +36 56 578 400 Fax: +36 56 578 401

sales@ffzrt.hu

www.ffzrt.hu

MEGAPROGRESS STAINLESS-STEEL TABLE TOPS

Table top

Model MTP

Smooth worktop made of 1.25 mm stainless steel, AISI 304, ground 320 grain and brushed to satin finish, turned down 40 mm on all sides.

The underside is fitted with V 20 particle board for noise insulation and also reinforced with an all-round frame. Panelled with stainless steel at front.

Max. length of a table top 3,850 mm continuous, extendable with screw joint.

Stainless stee	I	
Art. No.	Depth mm	Thickness mm
MC0001	up to 650	40
MC0003	up to 850	40



Table top


Model MTPB

Smooth worktop made of 1.25 mm stainless steel, AISI 304, ground in 320 grain and brushed to satin finish, turned down 40 mm on all sides.

The underside is fitted with V 20 particle board for noise insulation and also reinforced with an all-round frame. Underside smooth panelled with stainless-steel sheet over entire surface.

Max. length of a table top 3,850 mm continuous, extendable with screw joint.

Stainless steel		
Art. No.	Depth mm	Thickness mm
MC0005	up to 650	40
MC0007	up to 850	40




Corner table top


without screw joint, without vertical shelf


Stainless steel			
Art. No.	Width mm	Depth mm	Description
MC0145	1000	1000	Model MTP, with depth of 700 mm
MC0146	1000	1000	Model MTPB, with depth of 700 mm


MEGAPROGRESS STAINLESS-STEEL TABLE TOP ACCESSORIES




Screw joint for stainless-steel table tops Art. No. 580130








Profile edge for MTP/MTPB model for stainless-steel table tops Stainless steel Art. No. Height mm MC0028 8



Vertical sh	nelf Z 40/20	Vert. shelf Z 40/20 front shortened, one-sided	Vert. shelf Z 150/20 one-sided
Stainless st	eel	Stainless steel	Stainless steel
Art. No.	Description	Art. No.	Art. No.
MC0030	at rear	MC0099	MC0098
MC0031	2-sided		
MC0032	3-sided		

MEGAPROGRESS STAINLESS-STEEL TABLE TOP ACCESSORIES



Fitting hole

for 28-35 mm dia.

Art. No.	Diameter mm
MC0029	28–35



with stainless-steel panelling (MTP) and sleeve

Art. No.

MC0103

Table top cut-out

Art. No.	Description
MC0100	L-shaped pillars mounted on wall
MC0101	L-shaped pillars mounted on front
MC0102	U-shaped pillars mounted on wall


Stamped grooved surface

Stainless steel				
Art. No.	Width mm	Depth mm	Description	
MC0033	600	400	without incline	
MC0034	600	400	with incline	



Art. No.

MC0036



Ventilation grate for stainless-steel table top


punched in

Stainless steel

Art. No.

538331

MEGAPROGRESS WELDED-IN BASIN



Welded-in basin (only in conjunction with stainless-steel table tops)


Stainless-steel basin

Stainless s	teel				
Art. No.	Width mm	Depth mm	Height mm	Description	
200855	240	340	150	Drain in centre, 1 ½"	
203400	240	370	150	Drain in centre, 1 ½"	
MC0090	370	340	150	Drain at rear right or left, 1 ½"	
MC0401	400	400	200	Drain at rear right or left (reversible), 1 ½"	
MC0083	400	400	250	Drain at rear right or left, 1 ½"	
MC0084	400	400	300	Drain at rear right or left, 1 ½"	
MC0142	500	400	250	Drain at rear right or left, 1 ½"	
MC0086	500	400	300	Drain at rear right or left, 1 ½"	
MC0087	500	500	250	Drain at rear right or left, 1 ½"	
MC0088	500	500	300	Drain at rear right or left, 1 ½"	
MC0089	500	500	350	Drain at rear right or left, 1 ½"	
602253	600	400	250	hand-welded Drain at rear right, 1 ½"	
602254	600	400	250	hand-welded Drain at rear left, 1 ½"	
MC0250	600	450	250	Drain on right or left, 1 ½"	
MC0143	600	450	300	Drain on right or left, 1 ½"	
MC0091	600	500	250	Drain at rear right or left, 1 ½"	
MC0092	600	500	300	Drain at rear right or left, 1 ½"	
MC0093	600	600	300	Drain at rear right or left, 1 ½"	
MC0094	700	600	300	Drain at rear right or left, 1 ½"	
Other dime	Other dimensions on request				

Note:

When installing the welded-in basins in MTBP stainless-steel table tops plus basin cut-out and sealing.


MEGAPROGRESS WELDED-IN BASIN



Hand-washing basin

Drain in centre, 1 1/2"


Stainless steel				
Art. No.	Width mm	Depth mm	Height mm	
MC0096	500	300	150	



Welded-in basin, round

without overflow, drain at centre rear, 1 $\frac{1}{2}$ ", basin size dia. 385 x 165 mm

Stainless stee	el		
Art. No.	Width mm	Depth mm	Height mm
511407	450	450	165



Welded-in infant bathtub

Drain at rear right, 1 1/2"

Stainless steel			
Art. No.	Width mm	Depth mm	Height mm
233746	720	420	300

Note: When installing the welded-in basins in MTBP stainless-steel table tops plus basin cut-out and sealing.




Top surface for welded-in basin

adjusted to basin size

Stainless steel	
Art. No.	Description
54958001	with handles, double-walled with rubber seal
54958002	with grip hole

MEGAPROGRESS HOSPITAL DRAIN



Hospital drain

Table top made of stainless steel with profile edge at front and welded-in utility sink $400 \times 400 \times 200$ mm, drain opening with edge rinsing, 345×345 mm, including 3-sided splash wall, with side panelling, incl. swingaway support rack, with edge rinsing

Stainless steel				
Art. No.	Width mm	Depth mm	Height mm	Description
542545	600	590	250	Model MAB 6 x 6 NW 70, with edge rinsing
542515	600	590	250	Model MAB 6 x 6 NW 100, with edge rinsing
542546	600	690	250	Model MAB 6 x 7 NW 70, with edge rinsing
542516	600	690	250	Model MAB 6 x 7 NW 100, with edge rinsing

Forming drain on top surface

Art. No.

MC0040

Odour trap for hospital drain

Model MAB 6 x 6 and Model MAB 6 x 7, adjustable, NW 70

Art. No.

137830

Odour trap for hospital drain

Model MAB 6 x 6 and Model MAB 6 x 7, fixed, NW 100

Art. No.

232044

Tank/pump system for hospital drain, Model ATT

Model "N", in accordance with DIN 1988, normal program with approx. 6 ltr. rinsing volume

Art. No.


245673

MEGAPROGRESS STAINLESS-STEEL BASIN ACCESSORIES



1 1/2" eccentric drain set

Synthetic	
Art. No.	Description
137195	with Bowden cable and pull knob, chrome-plated, without overflow



$1 \frac{1}{2}$ " tube overflow with rubber taper

Stainless steel	
Art. No.	Description
369961	with rubber taper, stainless-steel basket strainer, without brazed union for basin depth 150 mm, water column 130 mm
369962	with rubber taper, stainless-steel basket strainer, without brazed union for basin depth 200 mm, water column 180 mm
369963	with rubber taper, stainless-steel basket strainer, without brazed union for basin depth 250 mm, water column 200 mm
369964	for drain with rubber taper, stainless-steel basket strainer, without brazed union for basin depth 300 mm, water column 250 mm



1 1/2" tube overflow with brass taper

Stainless stee	I
Art. No.	Description
340583	heavy model, with brass taper and basket strainer for basin depth 150 mm, water column 130 mm
340584	heavy model, with brass taper and basket strainer for basin depth 200 mm, water column 180 mm
340585	heavy model, with brass taper and basket strainer for basin depth 250 mm, water column 200 mm
369965	heavy model, with brass taper and basket strainer for basin depth 300 mm, water column 250 mm

MEGAPROGRESS STAINLESS-STEEL BASIN ACCESSORIES



Odour trap

Synthetic	
Art. No.	Description
137267	Siphon, 1½" synthetic pipe odour trap with adjustable drain, 50 mm dia. outlet




Accessories for stainless-steel basins

Synthetic	
Art. No.	Description
369969	1½" synthetic drain connection for double basin units



Collar cover

Synthetic	
Art. No.	Description
137832	Synthetic collar cover, white, NW 50, for use with 137267



Cover plate for drain trap

Art. No.	Description
602154	2-piece with hole for odour trap for cut-out in cabinet rear wall

MEGAPROGRESS FITTINGS AND MIXER TAPS



BLANCO ANTAS

Chrome, drain can be swivelled 360°, hole for tap with 0.35 mm required, cartridge with ceramic disk technology, flexible connection tubes of 450 mm in length with 3/4" nut for especially easy and secure assembly, patented stream controller for significantly reduced calcification, ND model with flow regulator to protect the boiler, stabilising plate for increased fitting stability for assembly in stainless-steel basins, LGA certified*, DVGW certified* (*for high-pressure model).

High-pressure	Low-pressure
Art. No.	Art. No.
515337	516103



BLANCO ANTAS-S

Chrome, drain can be swivelled 140°, hole for tap with 0.35 mm required, cartridge with ceramic disk technology, shower hose with metal casing, flexible connection tubes of 450 mm in length with 3/4" nut for especially easy and secure assembly, patented stream controller for significantly reduced calcification, ND model with flow regulator to protect the boiler, stabilising plate for increased fitting stability for assembly in stainless-steel basins, equipped with non-return valve as standard to prevent backflow in acc. with EN 1717, LGA certified*, DVGW certified* (*for high-pressure model).

High-pressure	Low-pressure
Art. No.	Art. No.
515348	516764



BLANCO ELIPSO II single-lever mixer tap

Chrome, high-pressure, drain can be swivelled 130° hole for tap with 35 mm dia. required, cartridge with ceramic disk technology, flexible connection tubes of 450 mm in length and 3/8" nut, patented stream controller for significantly reduced calcification, stabilising plate for increased fitting stability for assembly in stainless-steel basins, LGA certified, DVGW certified.

Art. No.

514879



BLANCO ELIPSO-S II single-lever mixer tap

Chrome, drain can be swivelled 115°, pull-out hand shower with 2 shower modes, hole for tap with 0.35 mm required, cartridge with ceramic disk technology, shower hose with metal casing, flexible connection tubes of 450 mm in length with 3/8" nut, patented stream controller for significantly reduced calcification, stabilising plate for increased fitting stability for assembly in stainless-steel basins, equipped with non-return valve as standard to prevent backflow in acc. with EN 1717, LGA certified, DVGW certified.

Art. No.

514847

MEGAPROGRESS FITTINGS AND MIXER TAPS




Medi-care single-lever mixer tap

DN 8 chrome-plated, clinic single-hole tap, drain can be swivelled, projection 200 mm, with clinic arm lever

Art. No.

543130



Vertical fitting for free-standing demineralised water column

Laboratory vertical column for demineralised water

with corner valve, control handle coloured in accordance with DIN 12920 (E DIN EN 13792), fitting EPS-coated, grey (RAL 7001), chemically nickel-plated inside, screw hose fitting flat-sealing with hose nozzle (10/13 mm diameter) and stream controller in accordance with DIN 12898, Perbunan sealing disc and washer with counter-nut. G 3/4 B connection thread, 100 mm long. Maximum pressure at rest 10 bar. Maximum operating temperature 70° C.

Art. No.	Height mm
542998	200



1/2" two-hole mixer tap

Wall tap

Spray wash arm for wall tap

Extension for wall mounting by an additional 60 mm

for two-hole mixer tap

Art. No.

137380

Art. No.

127579



1/2" two-hole mixer tap

Vertical fitting

with swivel faucet, can be switched over to hand shower, with automatically closing valve KWC, shower projection 400 mm,

tube riser wall distance 60 mm, table height to UK shower head 270 mm, total height 1060 mm, hole spacing 153 mm, 22 mm dia. hole

Stainless steel	
Art. No.	Height mm
137379	1060

MEGAPROGRESS FITTING AND MIXER TAP ACCESSORIES




11/2" cleaning nozzle

with 8 attachments $\frac{3}{4}$ and 1.5 m metal hose, including table collar

Art. No.

145310



Compressed-air elbow connector for cleaning gun

Art. No.

600060

Table collar for additional cleaning nozzle

without hose taper, 35 mm dia. hole

Art. No.

145311

Shutoff valve

3/4" shutoff valve 35 mm dia. hole

Art. No.

530090


MEGAPROGRESS TABLE TOP ACCESSORIES - GENERAL



Vertical splash guard made of Plexiglas

with or without cut-out for vertical shelf, each incl. $3\,x$ open bracket and $1\,x$ closed bracket for front, size up to max. W = 665 mm, H = 490 mm


Art. No.	Description	Width mm	Depth mm	Height mm
543037	Vertical splash guard made of Plexiglas with or without cut-out for vertical shelf, incl. 3 x open holders, 1 x closed holder			
54309101	Vertical splash guard made of laminated safety glass for base cabinet, incl. 2x solid holders made of stainless steel	6	400	510
54309102	Vertical splash guard made of laminated safety glass for base cabinet, incl. 2x solid holders made of stainless steel	6	500	510
54309103	Vertical splash guard made of laminated safety glass for below wall cabinet, with cut-out for Thebo lamp, incl. 3x solid holders made of stainless steel	6	400	510
54309104	Vertical splash guard made of laminated safety glass for below wall cabinet, with cut-out for Thebo lamp, incl. 3x solid holders made of stainless steel	6	500	510
54309105	Vertical splash guard made of laminated safety glass for below wall cabinet, with cut-out for Thebo lamp, incl. 3x solid holders made of stainless steel	6	500	400
54309106	Vertical splash guard made of laminated safety glass for below wall cabinet without lamp, incl. 3x solid holders made of stainless steel	6	400	510
54309107	Vertical splash guard made of laminated safety glass for below wall cabinet without lamp, incl. 3x solid holders made of stainless steel	6	500	510
54309108	Vertical splash guard made of laminated safety glass for below wall cabinet without lamp, incl. 3x solid holders made of stainless steel	6	500	400



Support wall


Stainless steel			Powder-coated
Art. No.	Depth mm	Description	Art. No.
53059001	580	for 740 mm working height	54059001
53059003	580	for 890 mm working height	54059003
53059002	680	for 740 mm working height	54069002
53059004	680	for 890 mm working height	54059004

MEGAPROGRESS TABLE TOP ACCESSORIES - GENERAL




Support foot

Stainless steel		
Art. No.	Depth mm	Description
54983601	550	for 740 mm working height, made of 40 mm tube
54983603	650	for 740 mm working height, made of 40 mm tube
54983602	550	for 890 mm working height, made of 40 mm tube
54983604	650	for 890 mm working height, made of 40 mm tube



Mounting angle

Stainless steel		
Art. No.	Depth mm	
536991	450	
531284	550	
531285	650	




Bracket

Model KO

Bracket in stainless-steel tube, variable height

Stainless steel				
Art. No.	Width mm	Description		
54298001	475	in 25 mm tube		
54298004	475	in 40 mm tube		
54298002	575	in 25 mm tube		
54298005	575	in 40 mm tube		
54298003	675	in 25 mm tube		
54298006	675	in 40 mm tube		




Base cabinet, open

Model MOB

Optional shelf


Powder-coate	ed .			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764001	450	557	700	54764001
53764002	600	557	700	54764002
53764003	900	557	700	54764003
53764004	1200	557	700	54764004
53764005	450	557	850	54764005
53764006	600	557	850	54764006
53764007	900	557	850	54764007
53764008	1200	557	850	54764008



Base cabinet with hinged door

- 1 hinged door, left or right-hand hinging 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764101	450	580	700	54764101
53764105	600	580	700	54764105
53764109	450	580	850	54764109
53764113	600	580	850	54764113




Base cabinet with hinged door

Model MFB2

- 2 hinged doors 2 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764201	900	580	700	54764201
53764203	1200	580	700	54764203
53764205	900	580	850	54764205
53764207	1200	580	850	54764207




Base cabinet with door and panel

Model MFBB1

- 1 hinged door, left or right-hand hinging
- 1 handle
- 1 basin trim panel, 150 mm high

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764301	450	580	850	54764301
53764305	600	580	850	54764305



Base cabinet with hinged doors and panel

Model MFBB2

- 2 hinged doors
- 2 handles 1 basin trim panel, 150 mm high

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764401	900	580	850	54764401
53764403	1200	580	850	54764403




Base cabinet with door and drawer

Model MFBS1

- 1 hinged door, left or right-hand hinging
- 2 handles
- 1 drawer, 150 mm high

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764501	450	580	700	54764501
53764505	600	580	700	54764505
53764509	450	580	850	54764509
53764513	600	580	850	54764513



Base cabinet with hinged doors and drawers

Model MFBS2

- 2 hinged doors
- 4 handles
- 2 drawers, 150 mm high

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764601	900	580	700	54764601
53764603	1200	580	700	54764603
53764605	900	580	850	54764605
53764607	1200	580	850	54764607




Base cabinet with tilt drawer

Model MKB

1 tilt drawer with pneumatic door brake, inside of door with fold-up hanging bars and shelf for synthetic garbage bags (60 ltr.), cannot be mounted below basin

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764701	450	580	850	54764701
53764702	600	580	850	54764702




Base cabinet with pull-out

Model MLTA

- 1 pull-out with 1 stainless-steel collection container
- 1 handle

Powder-coat	Powder-coated				St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
53764801	300	580	850	Dimensions of stainless-steel collection container: 195 x 425 x 550 mm or: 195 x 425 x 450 mm	54764801
53764802	450	580	850	Dimensions of stainless-steel collection container: 345 x 425 x 550 mm or: 345 x 425 x 450 mm	54764802



Base cabinet with waste separation system

Model MLTAS


1 manual extension

1 handle

integrated waste separation system

with 3 synthetic buckets (1 x 18.5 ltr.; 2 x 16 ltr.)

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53763301	600	580	850	54763301



Base cabinet with waste separation system

Model MLTASK

- 1 pull-out with foot operation 1 basin trim panel, 150 mm high

Powder-coat	Powder-coated				St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
54200302	450	580	850	integrated waste separation system with 2 buckets (2 x 18.0 ltr.)	54200402
54200303	450	580	850	integrated waste separation system with 3 buckets (1 x 18.0 ltr.; 2 x 8 ltr.)	54200403
54200301	600	580	850	integrated waste separation system with 3 buckets (1 x 18.5 ltr.; 2 x 16 ltr.)	54200401




Base cabinet with waste separation system and basin trim panel

Model MLTASB

- 1 manual extension
- 1 basin trim panel
- 1 handle

Powder-coated					St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
53790202	450	580	850	integrated waste separation system with 3 buckets (1 x 18.5 ltr.; 2 x 8 ltr.)	54243302
53790201	600	580	850	integrated waste separation system with 3 buckets (1 x 18.5 ltr.; 2 x 8 ltr.)	54243301



Base cabinet with drawers

Model MLT/3

3 drawers, 200 mm high each

3 handles

Powder-coate	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53765001	450	580	700	54765001	
53765003	600	580	700	54765003	
53765002	900	580	700	54765002	
53765004	1200	580	700	54765004	




Base cabinet with drawers

Model MLT/3

- 2 drawers, 300 mm high each 1 drawer, 150 mm high 3 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765005	450	580	850	54765005
53765007	600	580	850	54765007
53765006	900	580	850	54765005
53765008	1200	580	850	54765007




Base cabinet with drawers

Model MLT/3

3 drawers, 250 mm high each

3 handles

Powder-coate	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53765009	450	580	850	54765009	
53765011	600	580	850	54765011	
53765010	900	580	850	54765010	
53765012	1200	580	850	54765012	



Base cabinet with drawers

Model MLT/4

- 4 drawers, 150 mm high each
- 4 handles


Powder-coated	i			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765013	450	580	700	54765013
53765015	600	580	700	54765015
53765014	900	580	700	54765014
53765016	1200	580	700	54765016



Base cabinet with drawers

- 3 drawers, 200 mm high each 1 drawer, 150 mm high
- 4 handles

Powder-coate	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53765017	450	580	850	54765017	
53765019	600	580	850	54765019	
53765018	900	580	850	54765018	
53765020	1200	580	850	54765020	



Base cabinet with drawers

Model MLT/4

with pull-out worktop

2 drawers, 200 mm high each 1 drawer, 150 mm high 1 pull-out worktop, 50 mm high

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765021	450	580	700	54765021
53765023	600	580	700	54765023



Base cabinet with drawers

Model MLT/5

with pull-out worktop

- 3 drawers, 150 mm high each 1 drawer, 100 mm high 1 pull-out worktop, 50 mm high

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765025	450	580	700	54765025
53765027	600	580	700	54765027



Base cabinet with drawers

Model MLT/5

5 drawers, 150 mm high each

5 handles

Powder-coated	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53765029	450	580	850	54765029	
53765031	600	580	850	54765031	
53765033	900	580	850	54765033	
53765035	1200	580	850	54765035	




Base cabinet with drawers and door

Model MLTF/5

- 1 door, left-hand hinging
- 3 drawers, 150 mm high, 450 mm wide each 2 drawers, 150 mm high, 900 mm wide each
- 6 handles


Powder-coated	Powder-coated			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765101	900	580	850	54765101



Base cabinet with drawers

- 3 drawers, 150 mm high, 300 mm wide each 1 drawer, 150 mm high, 600 mm wide
- 1 drawer, 300 mm high, 600 mm wide
- 2 drawers, 150 mm high, 900 mm wide each
- 7 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765201	900	580	850	54765201




Base cabinet with sliding doors

Model MSB

2 sliding doors 35 mm guide plate 2 handles

Powder-coate	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53765301	900	580	850	54765301	
53765303	1200	580	850	54765303	
53765305	1500	580	850	54765305	



Base cabinet with sliding doors and basin trim panel


Model MSBB

2 sliding doors

2 handles

1 basin trim panel, 150 mm high

Powder-coate	Powder-coated			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765401	900	580	850	54765401
53765403	1200	580	850	54765403
53765405	1500	580	850	54765405




Corner base cabinet

Model MEBE

- 1 hinged door, left or right-hand hinging 1 fixed shelf 1 handle


Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765501	900	580	850	54765501



Corner base cabinet

- 1 hinged door, left or right-hand hinging 2 rotating shelves
- 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765601	900	580	850	54765601




Corner base cabinet

Model MEBK

1 tilt drawer with pneumatic door brake, inside of door with fold-up hanging bars and shelf for synthetic garbage bags

Powder-coated	Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762501	900	580	850	54762501



Base cabinet with hinged doors for DIN module

Model EMFB2

2 hinged doors

1 centre partition wall


2 handles

without equipment

for mounting DIN modules, size 535 x 500 mm

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53770501	1200	580	700	54770501
53770503	1200	580	850	54770503

MEGAPROGRESS BASE CABINET - REFRIGERATION UNIT




Base cabinet for drug refrigerator

Model MFBK

Price without refrigeration unit 1 front-mounted door, left or right-handed door hinging lockable with lever lock, ventilation grate for the integration of a drug refrigerator, Kirsch, Med. 85, 80 ltr. or Froster Med 70 1 handle

Powder-coated			Stainless steel	
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765701	600	580	850	54765701




Base cabinet refrigerator

Model MUK

Door hinging on right or left Base cabinet refrigerator, approx. 150 ltr., adjustable from $+2^{\circ}$ to + 10° C, with automatic defroster and -18°C freezer compartment Liebherr KUw 1544, with decorative trim panel in front colour, connection 230 V–110 W (other makes on request)

Powder-coated	i			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765801	600	580	850	54765801

MEGAPROGRESS BASE CABINET WITH WARMING DEVICE



Heating cabinet - base cabinet


Model MFBW1

- NOT SUITABLE FOR STORING INFUSIONS -

- 1 lockable hinged door, left or right-hand hinging
- 1 stainless-steel cabinet shelf, perforated
- 1 handle

Output 1000 W

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53765901	600	580	850	54765901



Heating cabinet - base cabinet

Model MFBW2

- NOT SUITABLE FOR STORING INFUSIONS -

- 2 lockable hinged doors
- 2 perforated cabinet shelves made of stainless steel
- 2 handles

Output 2000 W

Powder-coate	d			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54208401	900	580	700	54208601
54208403	1200	580	700	54208603
54208405	900	580	850	54208605
54208407	1200	580	850	54208607

MEGAPROGRESS WARMING DRAWER



Warming drawer for infusions

with perforated insert, switch panel and LED display for display of inside temperature Capacity: drawer 450 mm wide: 12 x 1 ltr. or 20 x 0.5 ltr. bottles; drawer 600 mm: 20 x 1 ltr. or 32 x 0.5 ltr. bottles; drawer 660 mm wide: 24 x 1 ltr. or 36 x 0.5 ltr. bottles, temperature adjustable from +33 $^{\circ}\text{C}$ to +37 $^{\circ}\text{C}$, set to + 37 $^{\circ}\text{C}$ at factory, overtemperature protection at 46 $^{\circ}\text{C}$, self-limiting PTC heating element, connected load: 220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A; frame height 233 mm, loading height: panel height minus 50 mm; Class 1 medical product

Powder-coated					St. steel
Art. No.	Width mm	Depth mm	Height mm	Connected load Rating	Art. No.
34678401	450 – 660	580-680	350 – 375	220-240 V AC, 50-60 Hz, 400 Watt, 1.7 A	34678402




Warming drawer for linens

with perforated insert, switch panel and LED display for display of inside temperature Temperature adjustable from 40 °C to 65 °C, overtemperature protection, self-limiting PTC heating element, connected load: 220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A;

connected load: 220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A; frame height 233 mm, loading height: trim panel height minus 50 mm; drawer capacity: 450 mm: 24 dm³, 600 mm: 34 dm³, 660 mm: 40 dm³

Powder-coated					St. steel
Art. No.	Width mm	Depth mm	Height mm	Connected load Rating	Art. No.
54306401	450 – 660	580	350 – 375	220-240 V AC, 50-60 Hz, 400 Watt, 1.7 A	54306402

MEGAPROGRESS BASE CABINET FOR DRAIN




Drain base cabinet

Model MBB

for hospital drain 1 revision panel, removable

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766201	600	580	600	54766201



Drain base cabinet

Model MFAB1

for hospital drain

Pressure increase system can be integrated


1 hinged door, left or right-hand hinging

lockable

1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766101	600	580	600	54766101

MEGAPROGRESS BASE CABINET FOR ULTRASOUND UNIT



Base cabinet for installing an ultrasound unit

Model MFBBUS2

- 2 hinged doors
- 2 handles
- 1 panel 150 mm high with cut-out for ultrasound unit control device

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766301	900	580	850	54766301



Bandelin ZE 1058 ultrasound unit

Model SONOREX ZE 1058 ST 15

Control unit with time switch for 1–15 minutes and continuous operation complete with Bandelin SONOREX ZE1058 ultrasonic cleaning device

Art. No.	Width mm	Depth mm	Height mm	Description
542988	600	400	200	consisting of GT1000M HF generator, max. output 2 x 1200 W/period, frequency 35 KHz, with 16 swivelling elements including TE1058 swivelling basin made of stainless steel, drain on either left or right, dim. 600 x 400 x 200 mm suitable for DIN-STU and ISO standard wire mesh basket, including drain set, basket carrier, insert basket and lid

MEGAPROGRESS BASE CABINET FOR ULTRASOUND UNIT



Bandelin ZE 1058 DT ultrasound unit

with ST 30 DT digital control unit with temperature control in swivelling basin and temperature sensor complete with Bandelin SONOREX ZE1058 ultrasonic cleaning device

Art. No.	Width mm	Depth mm	Height mm	Description
543225	600	400	200	consisting of GT1000M HF generator, max. output 2 x 1200 W/period, frequency 35 KHz, with 16 swivelling elements, including TE1058 swivelling basin made of stainless steel, drain at right or left, dim. 600 x 400 x 200 mm suitable for DIN-STU and ISO standard wire mesh basket, including drain set, basket carrier, insert basket and lid



Bandelin ultrasound unit control unit

ST 30 DT

Art. No.	Description
MC0106	STE 30 DT digital control unit for SONOREX Super ZE 1058 ultrasound unit (ST 15 control unit is eliminated)

MEGAPROGRESS BASE CABINET FOR ULTRASOUND UNIT



SONOMIC MC 1000 ultrasound unit, complete

Model SONOMIC MC 1000

Bandelin ultrasound unit for hollow bodies for disinfection and cleaning of max. 12 washable MIC instruments with K 1000 MC basket and D 1000 MC lid Table-top unit

Stainless stee	el				
Art. No.	Width mm	Depth mm	Height mm	Thick- ness mm	Description
542989	860	490	415	2	Swivelling basin, inside: 650 x 400 x 210/230* mm (LxWxD), *angled well bottom, working filling capacity: 35 ltr., drain: fitting with rotary handle operation, vibration system: 12 PZT large-area vibration system, ultrasound frequency: 40 kHz, peak ultrasound output: 2400 W, HF output: 600 W, maintenance heating 400 W, current consumption: 2.9 A, weight with basket and lid: 40 kg Stainless steel 1.4571, titanium-stabilised, 2 mm thick

Medisafe ultrasound unit, complete

Model MED 1134 SI Digital

complete with accessories, for 6 to 12 hollow instruments

Art. No.	Width mm	Depth mm	Height mm	Description
542990	656	301	156	Cut-out dimensions: 656 x 301 mm Basin dimensions: 651 x 294 x 156 mm

MEGAPROGRESS GYNAECOLOGY CABINET




Gynaecology base cabinet

Model MLTW

- 2 drawers, 150 mm high each
- 4 drawers, 100 mm high each with preheating device
- 1 switch panel, 50 mm high
- 6 handles

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
53763501	500	580	850
53763503	600	580	850

MEGAPROGRESS PLASTER BENCH SYSTEM AND ACCESSORIES



Stainless steel			
Art. No.	Width mm	Depth mm	Height mm
MC0135	2720	600	890

Plaster bench system

Model MGA 27/9

Stainless-steel table top with

2 welded-in basins

 $400 \times 400 \times 200$ mm, with all-round profile edge and incline towards basins


Measuring marks stamped in on front turned down edge

- 1 base cabinet, 600 mm wide with hinged door, left or right-hand hinging, with 1 cabinet shelf made of stainless steel
- 1 base cabinet, 900 mm wide, with 6 drawers, 150 mm high each and 1 drawer, 300 mm high
- in basin area
- 1 panel, 1200 mm long and 255 mm high
- 8 handles

Art. No.			
MC0035			

Measuring marks for plaster bench

MEGAPROGRESS PLASTER BENCH SYSTEM AND ACCESSORIES



1½" tube overflow

Stainless steel	
Art. No.	Description
369962	with rubber taper, basket strainer made of stainless steel without brazed union for basin depth of 200 mm, water level 180 mm



Drain connection

Synthetic		
Art. No.	Description	
369969	1½" synthetic drain connection for double basin units	




Plaster sedimentation basin, mobile

Model EWL 90

Art. No.	Width mm	Height mm	Description
543022	560	585	90 litre capacity


MEGAPROGRESS PLASTER BENCH SYSTEM AND ACCESSORIES



Synthetic plaster catch basin

Model 35 W


Art. No.	Description
146292	for wall mounting, can be pulled out for disposal



Synthetic plaster catch basin

Model 35 T

Art. No.	Description
146317	for cabinet mounting, can be pulled out for disposal




High cabinet - open

Model MOBH

Optional shelves

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53767201	450	557	2100	54767201
53767202	600	557	2100	54767202
53767203	900	557	2100	54767203
53767204	1200	557	2100	54767204




High cabinet with hinged door

Model MFBH1

- 1 hinged door, left or right-hand hinging 1 handle

Powder-coated	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53767301	450	580	2100	54767301	
53767305	600	580	2100	54767305	




High cabinet with hinged doors

Model MFBH2

- 2 hinged doors
- 2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53767401	900	580	2100	54767401
53767403	1200	580	2100	54767403




High cabinet with hinged door with glass insert

Model MGBH1

Hinged door with glass insert, left or right-hand hinging 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762601	450	580	2100	54762601
53762605	600	580	2100	54762605




High cabinet with hinged doors with glass insert

Model MGBH2

- 2 hinged doors with glass insert 2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762701	900	580	2100	54762701
53762703	1200	580	2100	54762703




High drug cabinet

Model MFMH1

- 1 hinged door, left or right-hand hinging
- 8 drug containers on the inside of the door (shelves shortened in accordance with accessories)

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53767901	600	580	2100	54767901




High drug cabinet

Model MFMH2

- 2 hinged doors
- 2 handles
- 16 drug containers on the inside of the door (shelves shortened in accordance with accessories)

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768001	900	580	2100	54768001
53768003	1200	580	2100	54768003



High drawer cabinet

Model MLTFH1

- 1 hinged door, left or right-hand hinging 5 drawers, 250 mm high each
- 6 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768301	600	580	2100	54768301



High drawer cabinet


Model MLTFH2/11

2 hinged doors

2 drawers, 100 mm high, 600 mm wide each 4 drawers, 150 mm high, 600 mm wide each 5 drawers, 150 mm high, 1200 mm wide each

13 handles

Powder-coated	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53790601	1200	580	2100	53790701	



High drawer cabinet


Model MLTFH2

2 hinged doors

5 drawers, 250 mm high each

7 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768401	900	580	2100	54768401



High OT accessories cabinet


Model MFOPH2

2 hinged doors

2 handles

Brackets and slide rails at left and rear (for 900 mm width), at left, right and rear (for 1200 mm width) on inner walls for mounting OT table accessories

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53770001	900	580	2100	54770001
53770003	1200	580	2100	54770003




High cabinet with roller shutter

Model MRBH

with anodised aluminium roller shutter

Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	
54296901	600	580	2100	



High cabinet with pull-out wall for instruments

Model MFIZM

with 1 pull-out perforated system wall (made of powder-coated steel), with handle, for hooking in a maximum of 60 system hooks per wall, individually adjustable, without accessories, max. total loading capacity: 130 kg $\,$

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
54238202	300	580	2100


System hooks for high cabinet with pull-out wall for instruments

Perforated wall hooks for perforated system wall, length 100 mm, hook-in bridge for 30 mm hole spacing, wire diameter 4 mm

Stainless steel

Art. No.

601790




High cabinet with hinged doors for DIN module

Model EMFBH2

- 2 hinged doors
- 1 centre partition wall
- 2 handles
- without equipment

Powder-coated					Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
53771101	1200	580	2100	for mounting DIN modules, size 535 x 500 mm	54771101




High cabinet with hinged doors with glass insert for DIN module

Model EMGBH2

- 2 hinged doors with glass insert
- 1 centre partition wall
- 2 handles
- without equipment

Powder-coated					Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
53790401	1200	580	2100	for mounting DIN modules, size 535 x 500 mm	53790501

MEGAPROGRESS IMPLANT CABINET



Implant base cabinet


Model MLTI

6 drawers with variable compartment dividers made of stainless steel for implants and accessories, 100 mm high each

1 drawer with variable compartment dividers made of stainless steel for implants and accessories, 150 mm high

all drawers with full extension; 7 handles, max. load per drawer: 40 kg if distributed evenly

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53789101	900	680	890	53789301



High implant cabinet

Model MLTFBHI

Implant cabinet

top:

1 top-mounted cabinet with 2 hinged doors

with synthetic small-parts housings for implants and accessories (top-mounted cabinet depth: 480 mm) bottom:

6 drawers with variable compartment dividers made of stainless steel for implants and accessories,

100 mm high each, 1 drawer with variable metal compartment dividers for implants and accessories,

150 mm high; with cover made of stainless steel 9 handles


Max. load per drawer: 40 kg if distributed evenly


Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54200101	900	480/680	2100	54200201


MEGAPROGRESS IMPLANT CABINET


Implant base cabinet accessories


Art. No.	Description						
610396	Drawer 1 + 2, H100, MLT	MPS					
	10 x divider drawer	118 x 480 x 42 mm	MPS	610378			
	2 x divider drawer	208 x 480 x 42 mm	MPS	610379			
	14 x compartment divider	118 x 42 mm	MPC	610384			
	2 x compartment divider	208 x 42 mm	MPC	610385			
610397	Drawer 3 + 4, H100, MLT	MPS					
	12 x divider drawer	118 x 480 x 42 mm	MPS	610378			
	2 x divider drawer	90 x 480 x 42 mm	MPS	610377			
610398	Drawer 5 + 6, H100, MLT	MPS					
	4 x divider drawer	118 x 480 x 42 mm	MPS	610378			
	6 x divider drawer	562 x 160 x 42 mm	MPS	610382			
	12 x compartment divider	160 x 42 mm	MPC	610386			
610399	Drawer 7, H150, MLTI MF	s					
	6 x divider drawer	118 x 480 x 69 mm	MPS	610381			
	1 x divider drawer	90 x 480 x 69 mm	MPS	610380			
	7 x compartment divider	118 x 69 mm	MPC	610387			
146748	Partition walls for BK-20	, yellow					
146747	Small parts magazine Bl	C-20, yellow 185 x 400	x 83 mm				
146750	Partition walls for BK-30	Partition walls for BK-30, yellow					
146749	Small parts magazine Bl	Small parts magazine BK-30, yellow 93 x 400 x 83 mm					
542994	Labels for implant cabinet,	BK 20 small-parts maga	zine for MRI	< 93			
542995	Labels for implant cabinet,	BK 30 small-parts maga:	zine for MRI	< 186			
		-					












High endoscopy cabinet

Model MFEZH1 1VT

- 1 hinged door, left or right-hand hinging
- 1 handle
- 1 vertical partition wall, can be pulled out toward front, with 4 endoscope holders

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768501	300	580	2100	54768501
53768505	450	580	2100	54768505
53768509	600	580	2100	54768509




High endoscopy cabinet

Model MFEZH1 2VT

- 1 hinged door, left or right-hand hinging
- 1 handl
- 2 vertical partition walls, can be pulled out toward front, with 8 endoscope holders

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768601	600	580	2100	54768601




High endoscopy cabinet

Model MFEZH2 2VT

- 2 hinged doors
- 2 handles
- 2 vertical partition walls, can be pulled out toward front,
- with 8 endoscope holders

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768701	900	580	2100	54768701



High endoscopy cabinet

Model MFEZH2 3VT


2 hinged doors

2 handles

3 vertical partition walls, can be pulled out toward front,

with 12 endoscope holders

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768801	900	580	2100	54768801



High endoscopy cabinet

Model MFEZ DRH 1VT

- 2 hinged doors as pass-through cabinet
- 2 handles

54303201

1 vertical partition wall, can be pulled out on both sides, with 4 endoscope holders


450

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.

600

2100

53303201




High endoscopy cabinet

Model MFEZ DRH 2VT

- 4 hinged doors as pass-through cabinet
- 4 handles
- 2 vertical partition walls, can be pulled out on both sides,
- with 8 endoscope holders

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
54303301	600	600	2100




High endoscopy cabinet

Model MFEZ DRH 3VT

- 4 hinged doors as pass-through cabinet
- 4 handles
- 3 vertical partition walls, can be pulled out on both sides,
- with 12 endoscope holders

Powder-coated

Art. No.	Width mm	Depth mm	Height mm	
54303401	900	600	2100	




High endoscopy cabinet with carousel

Model MFEKH1

with carousel with 8 endoscope holders

1 hinged door, 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54303501	600	580	2100	54323001




High endoscopy cabinet with carousel

Model MFEKDRH1

with carousel with 8 endoscope holders 2 hinged doors as pass-through cabinet, 2 handles

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
54303601	600	600	2100

MEGAPROGRESS CATHETER CABINET




High catheter cabinet

Model MFHZH1 1VT

- 1 vertical extension with 12 hooks
- 1 handle
- Optional:
- U-shaped stainless-steel bar for holding catheter ends

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54238201	300	580	2100	54251801



High catheter cabinet

Model MFHZH1 2VT

2 vertical extensions with 12 hooks each


2 handles

Optional:

U-shaped stainless-steel bar for holding catheter ends

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54238001	600	580	2100	54251901

MEGAPROGRESS CATHETER CABINET



High catheter cabinet

Model MFHZH1 3VT


3 vertical extensions with 12 hooks each

3 handles

Optional:

U-shaped stainless-steel bar for holding catheter ends

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54238101	900	580	2100	54252001



Bar for holding catheter ends


U-shaped bar for vertical extensions

Stainless steel

Art. No.

604513

MEGAPROGRESS DRUG CABINET




High drug cabinet

Model MLTAH/1

- 1 vertical drug pull-out, 300 mm wide, lockable,
- 10 adjustable compartment inserts and 40 crosswise dividers made of Plexiglas 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53768901	300	580	2100	54768901



High drug cabinet

Model MLTAH/2


2 vertical drug pull-outs, 300 mm wide each,

with central lock,

20 adjustable compartment inserts and 80 crosswise dividers made of Plexiglas

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769001	600	580	2100	54769001

MEGAPROGRESS DRUG CABINET



High drug cabinet


Model MLTAH/3

3 vertical drug pull-outs, 300 mm wide each,

with central lock,
30 adjustable compartment inserts and 12 crosswise dividers made of Plexiglas 3 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769101	900	580	2100	54769101

MEGAPROGRESS PRACTICE CABINET



Practice cabinet


Model MPFG1

top: 1 hinged door with glass insert, left or right-hand hinging bottom: 1 hinged door, left or right-hand hinging lockable

4 glass cabinet shelves

2 handles

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
53789801	600	480	1750



Practice cabinet


Model MPFG2

top: 2 doors with glass insert and stop bar, with 4 glass cabinet shelves

bottom: 2 doors with stop bar, lockable

2 handles

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
53789901	1200	480	1750



High cabinet for drug refrigerator

Model MLTKH

equipped for the installation of a drug refrigerator (centre),


Kirsch Med. 85, 80 ltr., with front-mounted door, flush with front, lockable,

1 hinged door at top, left or right-hand hinging

bottom: 1 pull-out worktop 50 mm high, 4 drawers, 150 high each

7 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769201	600	580	2100	54769201



High cabinet for drug refrigerator

Model MLTKOH

equipped for the installation of a drug refrigerator (top),


Kirsch Med. 85, 80 ltr., with front-mounted door, flush with front, lockable,

1 hinged door in middle, left or right-hand hinging

bottom: 1 pull-out worktop 50 mm high, 4 drawers, 150 high each

7 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769301	600	580	2100	54769301



High cabinet for drug refrigerator


Model MFBKH

equipped for the installation of a drug refrigerator (centre),

Kirsch Med. 85, 80 ltr., with front-mounted door, flush with front, lockable, 1 hinged door each at top and bottom, left or right-hand hinging

- 1 pull-out worktop at bottom, 50 mm high
- 4 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769401	600	580	2100	54769401



High cabinet for drug refrigerator


Model MFBKOH

equipped for the installation of a drug refrigerator (top),

Kirsch Med. 85, 80 ltr., with front-mounted door, flush with front, lockable,

- 1 hinged door in middle and bottom, left or right-hand hinging
- 1 pull-out worktop between, 50 mm high
- 4 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769501	600	580	2100	54769501



High cabinet for refrigerator

Model MLTHKH


equipped for the installation of a drug refrigerator (top), Liebherr EK 1614, with freezer compartment, 127 ltr.,

bottom: 1 pull-out worktop, 50 mm high

1 drawer 150 mm high, 3 drawers, 200 high each

5 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769601	600	580	2100	54769601



High cabinet for refrigerator


Model MFBHKH

equipped for the installation of a drug refrigerator (top), Liebherr EK 1614, with freezer compartment, 127 ltr.,

bottom: 1 pull-out worktop, 50 mm high and 1 hinged door, left or right-hand hinging

2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53769701	600	580	2100	54769701



High cabinet for drug refrigerator


Model MFBKGBH

centre: compartment with front-mounted door, lockable, suitable for the installation of

- MED-100 drug refrigerator
- Froster MED-95
- BL-100 stored blood refrigerator

top: 1 hinged door, left or right-hand hinging bottom: 1 pull-out worktop, 50 mm high and 1 hinged door, left or right-hand hinging 4 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762101	600	580	2100	54762101



High cabinet for refrigeration units

Model MFBKGB2H

suitable for the installation of

- MED-100 drug refrigerator
- Froster MED-95
- BL-100 stored blood refrigerator
- 2 compartments with front-mounted door, lockable for refrigeration unit installation
- 2 handles

Powder-coated		Stainless steel		
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54202901	600	580	2100	54236201



High cabinet for refrigeration unit

Model MLTKGBH

centre compartment with front-mounted door, lockable

suitable for the installation of


- MED-100 drug refrigerator
- Froster MED-95
- BL-100 stored blood refrigerator

top: 1 hinged door, left or right-hand hinging

bottom: 1 pull-out worktop 50 mm high, 4 drawers, 150 high each

7 handles

Powder-coated		Stainless steel		
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762201	600	580	2100	54762201



High cabinet for drug refrigerator


Model MFBKH1

equipped for the installation of a drug refrigerator (centre),

Kirsch Med. 125, 120 ltr., with front-mounted door, flush with front, lockable,

- 1 hinged door each at top and bottom, left or right-hand hinging
- 1 pull-out worktop at bottom, 50 mm high
- 4 handles

Powder-coated		Stainless steel		
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54293501	600	580	2100	54293701



High cabinet for drug refrigerator

Model MLTKH1

equipped for the installation of a drug refrigerator (centre),

Kirsch Med. 125, 120 ltr., with front-mounted door, flush with front, lockable,


top: 1 hinged door, left or right-hand hinging

bottom: 1 pull-out worktop 50 mm high, 4 drawers, 150 high each

7 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54293601	600	580	2100	54293801

MEGAPROGRESS HIGH HEATING CABINET



High heating cabinet


Model MFBWH1

- NOT SUITABLE FOR STORING INFUSIONS -

- 1 lockable hinged door, left or right-hand hinging
- 5 perforated cabinet shelves made of stainless steel
- 1 handle

Output 1000 W

Powder-coated		Stainless steel		
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53770101	600	580	2100	54770101



High heating cabinet

Model MFBWH2


- NOT SUITABLE FOR STORING INFUSIONS -

- 2 lockable hinged doors
- 5 perforated cabinet shelves made of stainless steel 2 handles

Output 2000 W

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54208301	900	580	2100	54208501
54208303	1200	580	2100	54208503

MEGAPROGRESS HIGH HEATING CABINET




High cabinet with warming device

Model MLTWH1

- NOT SUITABLE FOR STORING INFUSIONS -

- 1 hinged door at top, left or right-hand hinging centred 1 warming compartment, output 1000 W,
- 2 perforated cabinet shelves made of stainless steel, lockable,
- door hinging on right or left
- 4 drawers below, 200 mm high each
- 6 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762301	600	580	2100	54762301



High cabinet with warming device


Model MFBSWH1

- NOT SUITABLE FOR STORING INFUSIONS -

- 1 hinged door each at top and bottom, left or right-hand hinging centred 1 warming compartment, lockable, output 1000 W, 2 perforated cabinet shelves made of stainless steel, door hinging on right or left
- 1 drawer below, 200 mm high
- 4 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762401	600	580	2100	54762401

MEGAPROGRESS COMBINATION CABINET



High cabinet with warming compartment and built-in refrigeration unit

Model MFBWKGH

- NOT SUITABLE FOR STORING INFUSIONS -

top: 1 hinged door, left or right-hand hinging centre: lockable compartment for installing MED-85 refrigeration unit or Froster MED-70 bottom: built-in warming compartment, lockable, with 2 perforated cabinet shelves made of stainless steel, output 1000 W

3 handles

Powder-coated	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762001	600	580	2100	54762001

MEGAPROGRESS WARMING DRAWER



Warming drawer for infusions

with perforated insert, switch panel and LED display for display of inside temperature Capacity: drawer 450 mm wide: 12 x 1 ltr. or 20 x 0.5 ltr. bottles; drawer 600 mm: 20 x 1 ltr. or 32 x 0.5 ltr. bottles; drawer 660 mm wide: 24 x 1 ltr. or 36 x 0.5 ltr. bottles, temperature adjustable from +33 $^{\circ}\text{C}$ to +37 $^{\circ}\text{C}$, set to +37 $^{\circ}\text{C}$ at factory, overtemperature protection at 46 $^{\circ}\text{C}$, self-limiting PTC heating element, connected load: 220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A; frame height 233 mm, loading height: trim panel height minus 50 mm; Class 1 medical product

Powder-coated Powder-coated					St. steel
Art. No.	Width mm	Depth mm	Height mm	Connected load Rating	Art. No.
34678401	450 – 660	580	350 – 375	220-240 V AC, 50-60 Hz, 400 Watt, 1.7 A	34678402




Warming drawer for linens

with perforated insert, switch panel and LED display for display of inside temperature Temperature adjustable from 40 $^{\circ}\text{C}$ to 65 $^{\circ}\text{C}$,

overtemperature protection, self-limiting PTC heating element, connected load: 220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A; frame height 233 mm, loading height: trim panel height minus 50 mm, drawer capacity: 450 mm: 24 dm³, 600 mm: 34 dm³, 660 mm: 40 dm³

Powder-coated Powder-coated				St. steel	
Art. No.	Width mm	Depth mm	Height mm	Connected load Rating	Art. No.
54306401	450 – 660	580-680	350 – 375	220–240 V AC, 50–60 Hz, 400 Watt, 1.7 A	54306402




Open wall cabinet

Model MHO

Optional shelves

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766401	450	277	600	54766401
53766402	600	277	600	54766402
53766403	900	277	600	54766403
53766404	1200	277	600	54766404
53766409	450	357	600	54766409
53766410	600	357	600	54766410
53766411	900	357	600	54766411
53766412	1200	357	600	54766412
53766405	450	277	750	54766405
53766406	600	277	750	54766406
53766407	900	277	750	54766407
53766408	1200	277	750	54766408
53766413	450	357	750	54766413
53766414	600	357	750	54766414
53766415	900	357	750	54766415
53766416	1200	357	750	54766416




Wall cabinet with hinged door

Model MHF1

- 1 hinged door, left or right-hand hinging
- 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766501	450	300	600	54766501
53766505	600	300	600	54766505
53766517	450	380	600	54766517
53766521	600	380	600	54766521
53766509	450	300	750	54766509
53766513	600	300	750	54766513
53766525	450	380	750	54766525
53766529	600	380	750	54766529




Wall cabinet with hinged doors

Model MHF2

- 2 hinged doors
- 2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766601	900	300	600	54766601
53766603	1200	300	600	54766603
53766609	900	380	600	54766609
53766611	1200	380	600	54766611
53766605	900	300	750	54766605
53766607	1200	300	750	54766607
53766613	900	380	750	54766613
53766615	1200	380	750	54766615




Wall cabinet with sliding doors

Model MHS

2 sliding doors 2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766701	900	300	600	54766701
53766703	1200	300	600	54766703
53766709	900	380	600	54766709
53766711	1200	380	600	54766711
53766705	900	300	750	54766705
53766707	1200	300	750	54766707
53766713	900	380	750	54766713
53766715	1200	380	750	54766715




Wall cabinet with roller shutter

Model MHR

with anodised aluminium roller shutter

Powder-coated			
Art. No.	Width mm	Depth mm	Height mm
54301701	600	380	600
54301702	900	380	750




Wall cabinet with hinged door with glass insert

Model MHG1

- 1 hinged door with glass insert, left or right-hand hinging

1 handle
Optional glass shelf


Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54281601	450	300	600	54287101
54281602	600	300	600	54287102
54281605	450	380	600	54287105
54281606	600	380	600	54287106
54281603	450	300	750	54287103
54281604	600	300	750	54287104
54281607	450	380	750	54287107
54281608	600	380	750	54287108



Wall cabinet with hinged doors with glass insert

with 2 hinged doors with glass insert, 2 handles, optional glass shelf

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54281501	900	300	600	54287201
54281502	1200	300	600	54287202
54281505	900	380	600	54287205
54281506	1200	380	600	54287206
54281503	900	300	750	54287203
54281504	1200	300	750	54287204
54281507	900	380	750	54287207
54281508	1200	380	750	54287208




Wall cabinet with folding door

Model MHK

- 1 folding door
- 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53766801	450	380	600	54766801
53766803	600	380	600	54766803
53766807	450	380	750	54766807
53766809	600	380	750	54766809



Wall cabinet with hinged doors for DIN module

Model EMHF2


- 2 hinged doors
- 1 centre partition wall
- 2 handles

for mounting DIN modules, size $538 \times 250 \text{ mm}$

without equipment

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53770801	1200	380	600	54770801

MEGAPROGRESS TOP-MOUNTED CABINET AS PER DIN STANDARD




Top-mounted cabinet with hinged door

Model MFBA1

- 1 hinged door, left or right-hand hinging
- 1 handle

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53767001	450	580	450	54767001
53767013	600	580	450	54767013
53767005	450	580	600	54767005
53767017	600	580	600	54767017
53767009	450	580	750	54767009
53767021	600	580	750	54767021




Top-mounted cabinet with hinged doors

Model MFBA2

- 2 hinged doors
- 2 handles

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53767101	900	580	450	54767101
53767107	1200	580	450	54767107
53767103	900	580	600	54767103
53767109	1200	580	600	54767109
53767105	900	580	750	54767105
53767111	1200	580	750	54767111

MEGAPROGRESS ISO MODULE BASE CABINET




Base cabinet with hinged door

Model SMFB1

- 1 hinged door, left or right-hand hinging

1 handle for mounting ISO modules, size 600 x 400 mm without interior equipment

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771209	660	480	700	54771209
53771201	460	680	700	54771201
53771213	660	480	850	54771213
53771205	460	680	850	54771205



Base cabinet with hinged doors

Model SMFB2


- 2 hinged doors
- 2 handles
- 1 centre partition wall

for mounting ISO modules, size 600 x 400 mm

without interior equipment

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771305	1320	480	700	54771305
53771301	920	680	700	54771301
53771307	1320	480	850	54771307
53771303	920	680	850	54771303

MEGAPROGRESS ISO MODULE BASE CABINET




Base cabinet with pull-out extensions

Model SMLT/3

3 ISO pull-out extensions, 250 mm high each, hanging frame with full extension 3 handles for mounting ISO modules, size 600 x 400 mm

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53789703	660	480	850	53790803
53789701	460	680	850	53790801




Base cabinet with pull-out extensions

Model SMLT/5

5 ISO pull-out extensions, 150 mm high each, hanging frame with full extension 5 handles for mounting ISO modules, size 600×400 mm

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53789707	660	480	850	53790807
53789705	460	680	850	53790805

MEGAPROGRESS ISO MODULE BASE CABINET




Base cabinet with tilt drawer

Model SMKB

1 tilt drawer with pneumatic door brake, inside of door with fold-up hanging bars and shelf for synthetic garbage bags (60 ltr.)

Powder-coated	d			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53764902	660	480	850	54764902
53764901	460	680	850	54764901

MEGAPROGRESS ISO MODULE HIGH CABINET



High cabinet with hinged door


Model SMFBH1

- 1 hinged door, left or right-hand hinging

1 handle without interior equipment,

for mounting ISO modules, size 600 x 400 mm

Powder-coate	d			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771801	460	680	2100	54771801
53771805	660	480	2100	54771805



High cabinet with hinged doors

Model SMFBH2

- 2 hinged doors
- 2 handles
- 1 centre partition wall

without interior equipment,

for mounting ISO modules, size 600 x 400 mm

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771901	920	680	2100	54771901
53771903	1320	480	2100	54771903

MEGAPROGRESS ISO MODULE HIGH CABINET



High cabinet with hinged door with glass insert


Model SMGBH1

- 1 hinged door with glass insert, left or right-hand hinging

1 handle without interior equipment, for mounting ISO modules, size 600 x 400 mm

Powder-coate	ed			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53763001	660	680	2100	54763001
53763005	660	480	2100	54763005

MEGAPROGRESS ISO MODULE HIGH CABINET



High cabinet with hinged doors with glass insert

Model SMGBH2

2 hinged doors with glass insert


2 handles

1 centre partition wall

without interior equipment,

for mounting ISO modules, size 600 x 400 mm

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53763101	920	680	2100	54763101
53763103	1320	480	2100	54763103




High cabinet with roller shutter

Model SMRBH

with anodised aluminium roller shutter without interior equipment, for mounting ISO modules, size 600 x 400 mm

Powder-coated	d			
Art. No.	Width mm	Depth mm	Height mm	Description
54296902	460	680	2100	without centre partition wall
54296903	920	680	2100	with centre partition wall
54296904	660	480	2100	without centre partition wall
54296905	1320	480	2100	with centre partition wall

MEGAPROGRESS ISO MODULE WALL CABINET



Wall cabinet with hinged door


Model SMHF1

- 1 hinged door, left or right-hand hinging

1 handle without interior equipment,

for mounting ISO modules, size 300 x 400 mm

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771401	460	380	600	54771401



Wall cabinet with hinged doors

Model SMHF2


- 2 hinged doors
- 2 handles
- 1 centre partition wall

without interior equipment,

for mounting ISO modules, size 300 x 400 mm

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771501	920	380	600	54771501

MEGAPROGRESS ISO MODULE WALL CABINET




ISO wall cabinet with roller shutter

Model SMHR

with anodised aluminium roller shutter, without interior equipment, for mounting ISO modules, size 300 x 400 mm

Powder-coated	t			
Art. No.	Width mm	Depth mm	Height mm	Description
54301703	460	380	600	without centre partition wall
54301704	920	380	600	with centre partition wall

MEGAPROGRESS ISO MODULE TOP-MOUNTED CABINET



Top-mounted cabinet with hinged door


Model SMFBA1

1 hinged door, left or right-hand hinging

1 handle without interior equipment,

for mounting ISO modules, size 600 x 400 mm

Powder-coated	Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Art. No.	
53771601	460	680	450	54771601	
53771605	460	680	600	54771605	
53771609	460	680	750	54771609	
53771613	660	480	450	54771613	
53771617	660	480	600	54771617	
53771621	660	480	750	54771621	



Top-mounted cabinet with hinged doors

Model SMFBA2

2 hinged doors

1 centre partition wall


2 handles

without interior equipment,

for mounting ISO modules, size 600 x 400 mm

Powder-coate	Powder-coated			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53771701	920	680	450	54771701
53771703	920	680	600	54771703
53771705	920	680	750	54771705
53771707	1320	480	450	54771707
53771709	1320	480	600	54771709
53771711	1320	480	750	54771711

MEGAPROGRESS MODULE EQUIPMENT



Multifunctional guide element

Synthetic guide rail with integrated clips, 15 kg loading capacity per element

Synthetic	
Art. No.	Description
343954	for DIN and ISO cabinets with 380 mm cabinet depth Length 290 mm
343953	for ISO cabinets with 480 mm cabinet depth Length 390 mm
343952	for DIN cabinets with 580 mm cabinet depth Length 490 mm
343951	for ISO cabinets with 680 mm cabinet depth Length 590 mm




Multifunctional telescopic pull-out

Metal guides with 2 securing elements made of stainless steel Ball-bearing castor model with pull-in mechanism and end lock Over-extension


Universal holding frame made of stainless steel Surface electropolished

Max. loading capacity of telescopic pull-out 30 kg



Stainless steel	
Art. No.	Description
542385	for ISO cabinets with 480 mm depth Guide length: 390 mm, can be pulled out to 450 mm
542384	for ISO cabinets with 680 mm depth Guide length: 590 mm, can be pulled out to 650 mm

MEGAPROGRESS STU HIGH CABINET




STU high cabinet with inner frame

Model CMFBHG1

with stainless-steel inner frame for mounting STU containers or STU baskets with hinged door, left or right-handed door hinging, cabinet without interior equipment, STU storage components optional, 1 handle,

1 segment for max. 11 x 1/2 STU

Powder-coate	ed			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54293101	400	680	2100	54293301



STU high cabinet with inner frame


Model CMFBHG2

with stainless-steel inner frame for mounting STU containers or STU baskets with 2 hinged doors,

cabinet without interior equipment, STU storage components optional,

Powder-coat	ted				St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
54293201	730	680	2100	2 segments for max. 22 x 1/2 STU	54293401
54293202	1060	680	2100	3 segments for max. 33 x 1/2 STU	54293402

MEGAPROGRESS STU HIGH CABINET




STU high cabinet with hinged door

Model CMFBH1

1 handle suitable for mounting STU containers or baskets, Wagner system

without interior equipment

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53772101	375	680	2100	54772101




STU high cabinet with hinged doors

suitable for mounting STU containers or baskets, Wagner system

- 2 hinged doors
- 1 centre partition wall
- 2 handles

without interior equipment

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53772201	750	680	2100	54772201



Roll-in cabinet


Model MFBHEE2

2 hinged doors with attached plinth

2 handles

Inside roll-in dimensions: 1080 x 820 x 2030 mm (W x D x H)

Powder-coated	i			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53762901	1200	920	2100	54762901



Roll-in, pass-through cabinet


Model MFBHDF2

 2×2 opposing hinged doors with attached plinth and electromagnetic locking, roll-up strip,

4 handles

Roll-in dimensions: 1080 x 820 x 2030 mm (W x D x H)

Powder-coate	Stainless steel			
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54239701	1200	920	2100	54238601




Pass-through cabinet

Model MFBDRH1

- 2 opposing hinged doors, left or right-hand hinging
- 2 handles with mutual electromagnetic locking, shelves optional

Powder-coate	d			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54200505	460	703	2100	54200805
54200501	600	703	2100	54200801



Pass-through cabinet

Model MFBDRH2

2 x 2 opposing hinged doors 4 handles with mutual electromagnetic locking

Optional shelves

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54200603	900	703	2100	54200703
54200601	1200	703	2100	54200701




Pass-through cabinet

Model MFBDRH2 MW

2 x 2 opposing hinged doors Centre partition wall 4 handles with mutual electromagnetic locking Optional shelves

Powder-coated	d			Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54305201	1200	703	2100	54243801




Pass-through cabinet

Model MFBHDR1

2 opposing hinged doors, left or right-hand hinging, lockable Optional shelves

Powder-coat	ed				St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
54239505	460	703	2100	2 handles, espagnolette lock with key actuation	54236705
54239511	460	703	2100	with espagnolette lock with rotary knob	54236711
54239501	600	703	2100	2 handles, espagnolette lock with key actuation	54236701
54239509	600	703	2100	with espagnolette lock with rotary knob	54236709




Pass-through cabinet

Model MFBHDF2

2 x 2 opposing hinged doors Centre partition wall 4 handles Optional shelves

Powder-coat	St. steel				
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
54239603	900	703	2100	4 handles, espagnolette lock with key actuation	54239403
54239606	900	703	2100	with espagnolette lock with rotary knob	54239406
54239601	1200	703	2100	4 handles, espagnolette lock with key actuation	54239401
54239605	1200	703	2100	with espagnolette lock with rotary knob	54239405

MEGAPROGRESS PASS-THROUGH COMPARTMENT SYSTEM




Pass-through cabinet

Model MFBHDR2 MW

2 x 2 opposing hinged doors Centre partition wall, lockable

Powder-coat	Powder-coated					
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.	
54243401	1200	703	2100	Centre partition wall, 4 handles, espagnolette lock with key actuation	54243401	
54243501	1200	703	2100	Centre partition wall, espagnolette lock with rotary knob	54243405	



Pass-through compartment system

Model MDF

self-supporting sturdy design, suitable for installation in wall openings or as room divider


Model:

4 compartments (dimensions of interior compartment: 358 x 657 x 457 mm),

1 hinged door per compartment at front, right or left-hand hinging lockable with rotary knob

Powder-coat	ted				St. steel
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.
54311201	400	680	2100	Rear open	53799801
54311202	400	703	2100	Rear with hinged door	53799802

MEGAPROGRESS PASS-THROUGH COMPARTMENT SYSTEM



Pass-through compartment system

Model MDFE


self-supporting sturdy design, suitable for installation in wall openings or as room divider Model:

4 compartments, 1 hinged door with rotary knob per compartment at front, right or left-hand hinging one hinged door at rear, mutual electromagnetic locking

Interior compartment dimensions: 350 x 625 x 455 mm

Top compartment 410 mm high

Powder-coated				Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
54307101	400	703	2100	54241801



Pass-through compartment system

Model SMDF

for ISO dimensions, self-supporting sturdy design, suitable for installation in wall openings or as room divider

Model:

4 compartments, 1 hinged door with rotary knob per compartment at front, right or left-hand hinging Compartment dimensions: 410 x 625 x 455 mm

Powder-coa	Powder-coated					
Art. No.	Width mm	Depth mm	Height mm	Description	Art. No.	
54311301	480	680	2100	Rear open	53799901	
54311302	480	703	2100	Rear with hinged door	53799902	


MEGAPROGRESS STU ACCESSORIES



STU support bracket

for hooking into pins, for STU cabinets with inner frame and STU shelf for storing containers and sterile equipment baskets


Stainless steel					
Art. No.	Width mm	Depth mm	Height mm		
542889	60	600	50		



Perforated shelf

for hooking into pins, for STU cabinets with inner frame and STU shelf for storing containers and sterile equipment baskets

Stainless steel	
Art. No.	
600777	



Closed shelf

for hooking into pins, for STU cabinets with inner frame and STU shelf for storing containers and sterile equipment baskets

Sta	inl	ess	stee

Art. No.

600778

MEGAPROGRESS STU ACCESSORIES




STU heavy-load extension


for storing containers and sterile equipment baskets.


1 rotary shelf and 2 support brackets with synthetic sliding rail, with 2/3 extension and pull-out stop, for hanging Max. load-bearing capacity 25 kg

Stainless stee	el		
Art. No.	Width mm	Depth mm	Description
542529	292	600	for hooking into pins, for STU cabinets with inner frame, STU shelf and container transport trolley
542952	292	600	for STU cabinet with laid-on slotted grid rails, with shelf carriers

MEGAPROGRESS PLINTH









Cabinet individual plinth

Powder-coated				Stainless steel
Art. No.	Width mm	Height mm	Cabinet depth mm	Art. No.
MC0148	450/460	100	457/657	MC0152
MC0149	600/660	100	457/657	MC0153
MC0150	900/920	100	457/657	MC0154
MC0151	1200/1320	100	457/657	MC0155




Cabinet individual plinth, levelable

Powder-coated				Stainless steel
Art. No.	Width mm	Height mm	Cabinet depth mm	Art. No.
MC0158	450/460	100	457/657	MC0162
MC0159	600/660	100	457/657	MC0163
MC0160	900/920	100	457/657	MC0164
MC0161	1200/1320	100	457/657	MC0165



Metal plinth plate

Powder-coated	Stainless steel
Art. No.	Art. No.
MC0138	MC0140



ISO cabinet shelf

for use with multifunction guide element and telescopic slide

Wood/synthetic		Shelf dimensions	
Art. No.	Width mm	Depth mm	Height mm
344493	600	400	12

ISO cabinet shelf for carrier wall

on underside with 4-sided fold-in, single-walled

Powder-coated		Shelf dimension	ins	Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
608727	600	400	12	345766

ISO cabinet shelves for cabinet with slotted grid

613

Single-walled, with shelf carrier set

53798021

Powder-coated		Shelf dimen	sions	Stainless steel
Art. No.	Width mm	Depth mm	Height mm	Art. No.
53798621	413	607	25	53793221
53798620	613	407	25	53793220
Wood/synthetic		Shelf dimen	sions	
Art. No.	Width mm	Depth mm	Height mm	
53798020	413	607	21	

407

21

Insert base with shelf carrier set

for base, top-mounted and high cabinet, 580 mm deep

Wood/synthetic		
Art. No.	Width mm	Depth mm
53798001	450	557
53798002	600	557
53798003	900	557
53798004	1200	557

Insert base with shelf carrier set

for base, top-mounted and high cabinet, 580 mm deep, single-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798601	450	557	53793201
53798602	600	557	53793202
53798603	900	557	53793203
53798604	1200	557	53793204

Insert base with shelf carrier set

for wall cabinet 300 mm deep

Wood/synthetic		
Art. No.	Width mm	Depth mm
53798005	450	277
53798006	600	277
53798007	900	277
53798008	1200	277

Insert base with shelf carrier set

for wall cabinet 380 mm deep

Wood/synthetic		
Art. No.	Width mm	Depth mm
53798009	450	357
53798010	600	357
53798011	900	357
53798012	1200	357

Insert base with shelf carrier set

for wall cabinet, 300 mm deep, single-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798605	450	277	53793205
53798606	600	277	53793206
53798607	900	277	53793207
53798608	1200	277	53793208

Insert base with shelf carrier set

for wall cabinet, 380 mm deep, single-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798609	450	357	53793209
53798610	600	357	53793210
53798611	900	357	53793211
53798612	1200	357	53793212

Insert base with shelf carrier set

for base, top-mounted and high cabinet, 580 mm deep, double-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798701	450	557	53798501
53798702	600	557	53798502
53798703	900	557	53798503
53798704	1200	557	53798504

Insert base with shelf carrier set

for wall cabinet, 300 mm deep, double-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798705	450	277	53798505
53798706	600	277	53798506
53798707	900	277	53798507
53798708	1200	277	53798508

Insert base with shelf carrier set

for wall cabinet, 380 mm deep, double-walled

Powder-coated			Stainless steel
Art. No.	Width mm	Depth mm	Art. No.
53798709	450	357	53798509
53798710	600	357	53798510
53798711	900	357	53798511
53798712	1200	357	53798512

Insert base with shelf carrier set

for wall cabinet 300 mm deep


Glass			
Art. No.	Width mm	Depth mm	Description
53798301	450	277	for wall cabinet 300 mm deep
53798302	600	277	for wall cabinet 300 mm deep
53798303	900	277	for wall cabinet 300 mm deep
53798304	1200	277	for wall cabinet 300 mm deep

Insert base with shelf carrier set

for wall cabinet 380 mm deep


Glass			
Art. No.	Width mm	Depth mm	Description
53798305	450	357	for wall cabinet 380 mm deep
53798306	600	357	for wall cabinet 380 mm deep
53798307	900	357	for wall cabinet 380 mm deep
53798308	1200	357	for wall cabinet 380 mm deep

MEGAPROGRESS SHELF



for practice cabinet, 480 mm deep, double-walled

Glass			
Art. No.	Width mm	Depth mm	Description
53798309	600	457	for practice cabinet, 480 mm deep
53798310	1200	457	for practice cabinet, 480 mm deep



Cabinet shelf securely screwed on

for 600 mm wide cabinet incl. mounting

Powder-coated		Stainless steel
Art. No.	Description	Art. No.
343466	single-walled	601347
601351	reinforced	601352



Waste collector, round

for installation in base cabinet Bin: stainless steel Ring and insert: synthetic Lid: synthetic

Stainless steel	
Art. No.	Volume
602153	11 litres

MEGAPROGRESS LIGHT PANELS AND ACCESSORIES

Thebo lamp

with glare protection

White			St. steel appear.
Art. No.	Width mm	Description	Art. No.
604501	321	Underframe lightning, Model R3200, 8 W	604505
604502	470	Underframe lightning, Model R3200, 15 W	604506
604509	625	Underframe lightning, Model R3200, 18 W	604510
604503	753	Underframe lightning, Model R3200, 16 W	604507
604504	927	Underframe lightning, Model R3200, 30 W	604508

Locking socket

white, for Thebo lamp

Art. No.	Description
601497	Locking socket
601947	Plug for locking socket

Connection unit

for Thebo lamp, 100 mm long

Art. No.	Description
601501	White
601502	Stainless-steel appearance

Connection unit with switch

for Thebo lamp, 130 mm long

Art. No.	Description
604511	White
604512	Stainless-steel appearance

Connection cable for plug coupling

for Thebo lamp

Art. No.	Description
601498	Plug coupling cable 200 mm
601499	Plug coupling cable 500 mm
601500	Plug coupling cable 2000 mm

MEGAPROGRESS LIGHT PANELS AND ACCESSORIES

Light panels without lighting

Powder-coated			Stainless steel
Art. No.	Height mm	Description	Art. No.
54311001	100	straight (first running metre) max. width per panel 2000 mm	54311011
54311002	100	straight (each further metre) up to max. width per panel 1000 mm	54311012
54311003	100	L-shaped (first running metre) max. width per panel 2000 m	54311013
54311004	100	L-shaped (each further metre) up to max. width per panel 1000 mm	54311014
54311005	100	U-shaped (first running metre) max. width per panel 1700 mm	54311015
54311006	100	U-shaped (each further metre) up to max. width per panel 1000 mm	54311016

Integrated LED underframe lightning for retrofitting

LED underframe lightning in wall cabinet, with outside cabinet floor, incl. transformer and switch

Powder-coated		Stainless steel
Art. No.	for cabinet width mm	Art. No.
54351711	450/460	54351715
54351712	600/660	54351716
54351713	900/920	54351717
54351714	1200/1320	54351718

Integrated LED underframe lightning for retrofitting

LED underframe lightning in wall cabinet, with outside cabinet floor, without transformer and switch

Powder-coated		Stainless steel
Art. No.	for cabinet width mm	Art. No.
54351719	450/460	54351715
54351720	600/660	54351716
54351721	900/920	54351717
54351722	1200/1320	54351718

MEGAPROGRESS LED LIGHT PANELS AND ACCESSORIES

Integrated LED underframe lightning

LED underframe lightning integrated in wall cabinet

incl. transf. and switch	Description	without transf. and switch
Art. No.	for cabinet width mm	Art. No.
54351701	450/460	54351705
54351702	600/660	54351706
54351703	900/920	54351707
54351704	1200/1320	54351708



LED interior lighting

integrated in wall cabinet, base cabinet or high cabinet

single-/double-hinged without dividing wall	Description		double-hinged with dividing wall
Art. No.	for cabinet height mm	Height mm	Art. No.
54351701	Wall cabinet 600 mm	600	54351705
54351702	Base cabinet 750 mm	750	54351706
54351703	High cabinet 2000 mm	2000	54351707

LED interior lighting

for drawer cabinet

Art. No.	Description	for drawer width mm	Width mm
54350101	first drawer (contains the power supply for each additional drawer)	600	600
54350111	Each additional drawer	600	600
54350102	first drawer (contains the power supply for each additional drawer)	900	900
54350112	Each additional drawer	900	900
54350103	first drawer (contains the power supply for each additional drawer)	1200	1200
54350113	Each additional drawer	1200	1200

MEGAPROGRESS ELECTRONIC LOCK AND ACCESSORIES

LS 200 electronic lock

PIN code furniture locking system with capacitive keypad, round rotary knob, standard deadbolt, for right and left-hand doors, incl. mounting materials and battery pack, with RFID programming and RFID MasterCode radio

Art. No.	Description
54350301	Installation direction A, vertical rotary knob at top
54350302	Installation direction B, vertical rotary knob at bottom
54350303	Installation direction C, horizontal rotary knob on left
54350304	Installation direction D, horizontal rotary knob on right

LS 300 electronic lock

RFID furniture locking system with contactless alarm sensor, round rotary knob, standard deadbolt, for right and left-hand doors, incl. mounting materials and battery pack

Art. No.	Description
54350401	Installation direction A, vertical rotary knob at top
54350402	Installation direction B, vertical rotary knob at bottom
54350403	Installation direction C, horizontal rotary knob on left
54350404	Installation direction D, horizontal rotary knob on right

LS 400 electronic lock


PIN code/RFID furniture locking system with combined PIN code and RFID technology, with contactless alarm sensor, round rotary knob, standard deadbolt, for right and left-hand doors, incl. mounting materials and battery pack

Art. No.	Description
54350503	Installation direction C, horizontal rotary knob on left
54350504	Installation direction D, horizontal rotary knob on right

Accessories for electronic lock

Art. No.	Description	
543511	Battery pack	for LS 200, 300, 400
543506	SystemKey set	for programming and managing a locking system, RFID cards in ISO format
543507	USB table-top reader	for programming SystemKeys and other RFID data carriers
543508	Lock Manager 6, Version Key	Software for LS 200, 300, 400, for programming and managing locking systems with SystemKeys
543509	MIFARE 4k RFID cards, 20-piece pack	RFID data carriers as cards, unprinted, uncoded
543510	Training/instruction plus tra	avel etc.

MEGAPROGRESS MEGACLICK, ACCESSORIES AND PARTITION WALL



FF-click

without panel rear wall, etc., only MEGAclick in panels

Art. No.	
54351201	one row – 5 MEGAclick connectors
54351202	one row – 8 MEGAclick connectors
54351203	two row - 2 x 5 MEGAclick connectors
54351204	two row - 2 x 8 MEGAclick connectors



MP crystal clear marking sign

PU 10 pc

Art. No. 543465

Steel sheet centre partition wall

- When retrofitting double-door cabinets, a new left-hand cabinet door is required -


Art. No.	Description
602145	for high cabinet, 557/657 x 2000 mm, with slotted grid
602146	for base cabinet, 557/657 x 750 mm, with slotted grid
602147	for wall cabinet, 357 x 750 mm, with slotted grid

Stainless-steel centre partition wall

- When retrofitting double-door cabinets, a new left-hand cabinet door is required -

Art. No.	Description
602148	for high cabinet, 557/657 x 2000 mm, with slotted grid
602149	for base cabinet, 557/657 x 750 mm, with slotted grid
602150	for wall cabinet, 357 x 750 mm, with slotted grid

MEGAPROGRESS NARCOTICS SAFE



Opiate narcotics safe in accordance with VDMA 24992, Safety level A

Steel sheet, powder-coated

with grid rail, with cabinet shelf

Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Description
246424	406	245	320	for wall cabinets Door hinging left
246425	406	245	320	for wall cabinets Door hinging right
246420	556	245	320	for wall cabinets Door hinging left
246421	556	245	320	for wall cabinets Door hinging right
246422	406	400	320	for high cabinets Door hinging left
246423	406	400	320	for high cabinets Door hinging right
246418	556	400	320	for high cabinets Door hinging left
246419	556	400	320	for high cabinets Door hinging right



Narcotics safe in accordance with EN 1143-1 Model 103-03

for high cabinets, with cabinet shelves

Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Description
542944	500	410	340	Right-hand hinging, inside dimensions: 416 x 295 x 230 mm (W x D x H), weight: 95 kg
601364	500	410	340	Left-hand hinging, inside dimensions: 416 x 295 x 230 mm (W x D x H), weight: 95 kg

MEGAPROGRESS NARCOTICS SAFE



Narcotics safe in accordance with EN 1143-1 Model 103-01

for high cabinets, with cabinet shelves


Powder-coated				
Art. No.	Width mm	Depth mm	Height mm	Description
601365	400	400	340	Left-hand hinging, inside dimensions: 316 x 270 x 230 mm (W x D x H), weight: 80 kg
542943	400	400	340	Right-hand hinging, inside dimensions: 316 x 270 x 230 mm (W x D x H), weight: 80 kg $$

Spare key for narcotics safe according to sample

Art. No.	Description
601791	for narcotics safes in accordance with EN 1143-1

Spare key for narcotics safe


Art. No.	Description
601336	for narcotics key with key no.



Hook rail for inside of door


in conjunction with shortened shelves

Stainless steel		
Art. No.	Width mm	
242055	300	
242056	450	



Stepped drug shelf for high cabinets - two-step

Powder-coated			
Art. No.	For cabinet width mm	Depth mm	Height mm
53799301	450	160	80
53799302	600	160	80
53799303	900	160	80
53799304	1200	160	80



Stepped drug shelf for high cabinets - three-step

Powder-coated			
Art. No.	For cabinet width mm	Depth mm	Height mm
53809901	450	300	120
53809902	600	300	120
53809903	900	300	120
53809904	1200	300	120



Art. No.	Width mm	Description
344204	450	Mounting of a file rack in a pull-out, 450 mm wide, complete frame
344273	450	Mounting of a file rack in a pull-out, 450 mm wide above lateral
344276	450	Mounting of a file rack in a pull-out, 450 mm wide above lateral



Angled support

stackable, synthetic, black required quantity depends on drawer height

Art. No.	Width	Depth	Height
	mm	mm	mm
543019	328	212	35



Door limiter incl. mounting

Art. No.	Description
345565	for high cabinet/wall cabinet
345567	for base cabinet

Clothes rod

mounted for high cabinet, consisting of oval clothes rod, chrome-plated with 2 mounts

Art. No.

602163



Ventilation grate for cabinet door

synthetic

Art. No.

Telescopic pull-out with angled mount, screwed on

Art. No.	Description
543020	Full extension, installation length 500 mm, pair
543021	Full extension, installation length 600 mm, pair

Desk utensil insert

with 8 compartments for use in pull-out worktop

Art. No.	Width	Depth	Height
	mm	mm	mm
145654	277	277	6

Interior drawer

Powder-coated	Stainless steel		
Art. No.	Width mm	Height mm	Art. No.
54324201	600	150	54342201
54324202	900	150	54342202
54324203	1200	150	54342203

Pull-out worktop below a cabinet shelf

for cabinet depth of 580 mm (dimensions = exterior dimensions incl. holder)

Duropal				
Art. No.	Width mm	Depth mm	Height mm	
537958	511	512	16	

Espagnolette lock for high cabinet

Art. No.	Description
340562	Key actuation
340563	with rotary knob

Lever lock for base or wall cabinet door or individual drawer

Art. No. 340564

Central locking for chest of drawers with up to 5 drawers

for model MLT, not suitable for ISO underframes

Art. No.

542023



FF MED U-handle

Art. No.

MEGAPROGRESS REFRIGERATION UNITS



Refrigerator

KUw 1544 Premium

Finish-compatible base cabinet refrigerator Liebherr KUw 1544, Gross/usable content 137/132 l

3-star freezer compartment with ice cube tray, automatic defroster in refrigeration section, "glass-line" placement shelves (1 of which can be separated), "glass-line" shelves, butter/cheese compartment, butter box, bottle/can holder, energy consumption: in 365 days 237.5 kWh, energy efficiency class A, niche dimensions in cm: 820 x 600 x 570 mm (H x W x D)

Art. No.	Description
145499	left-hand door hinging
145500	right-hand door hinging



EK 16-20 refrigerator

Finish-compatible EK 1614-20 built-in refrigerator - gross/usable content 127/121 ltr.

3-star freezer compartment with ice cube tray, energy consumption: in 365 days 193.4 kWh, energy efficiency class A+, niche dimensions in cm: $874-878 \times 560-570 \times min. 550 \ mm$ (H x W X D)

Art. No.

146099



MED-85 drug refrigerator

Kirsch MED-85 drug refrigerator for built-in and under-surface mounting

Cooling capacity 80 ltr.

Normal consumption 0.6 kWh/24 h

Exterior dimensions (incl. wall spacing) 470 x 510 x 740 mm (W x D x H)

Art. No.

MEGAPROGRESS REFRIGERATION UNITS



MED-100 drug refrigerator

Kirsch MED-100 drug refrigerator for built-in and under-surface mounting Door hinging right/left (can be changed) Exterior dimensions $540 \times 530 \times 820$ mm (W x D x H)

Art. No.

247348



MED125 drug refrigerator

Kirsch MED-125 drug refrigerator for built-in and under-surface mounting Cooling capacity 120 ltr. Normal consumption 0.55 kWh/24 h Exterior dimensions (incl. wall spacing) 540 x 535 x 810 mm (W x D x H)

Art. No.	Width mm	Depth mm	Height mm	Description
600933	540	535	810	left-hand door hinging
600934	540	535	810	right-hand door hinging



FROSTER-MED-70 freezer

Kirsch FROSTER-MED-70 freezer for built-in and under-surface mounting Cooling capacity 70 ltr.

Normal consumption 1.6 kWh/24 h

Exterior dimensions without table top 470 x 510 x 740 mm (W x D x H) $\,$

Art. No.

MEGAPROGRESS REFRIGERATION UNITS



FROSTER-MED-95 freezer

Kirsch FROSTER-MED-95 freezer for built-in and under-surface mounting Cooling capacity 95 ltr.

Normal consumption 2.8 kWh/24 h

Exterior dimensions without table top 540 x 530 x 820 mm (W x D x H)

Art. No.

247349



BL-100 stored blood refrigerator

Kirsch BL-100 stored blood refrigerator for built-in and under-surface mounting Cooling capacity $95\ \text{ltr.}$

Normal consumption 0.35 kWh/24 h

Exterior dimensions without table top 540 x 530 x 820 mm (W x D x H)

Art. No.

MEGAPROGRESS PANELS AS PER DIN AND ISO STANDARD, POWDER-COATED

Panels for cabinets as per DIN and ISO standard, powder-coated

Powder-coated			
Art. No.	Width mm	Height mm	Description
54056901	450/460	up to 200	Ceiling panel with fastening materials, low
54056902	600/660	up to 200	Ceiling panel with mounting materials, low
54056903	900/920	up to 200	Ceiling panel with mounting materials, low
54056904	1200/1320	up to 200	Ceiling panel with mounting materials, low
54057901	450/460	up to 200	Ceiling panel, closed at bottom, with mounting materials
54057902	600/660	up to 200	Ceiling panel, closed at bottom, with mounting materials
54057903	900/920	up to 200	Ceiling panel, closed at bottom, with mounting materials
54057904	1200/1320	up to 200	Ceiling panel, closed at bottom, with mounting materials
54057001	450/460	200-900	Ceiling panel with mounting materials, high
54057002	600/660	200-900	Ceiling panel with mounting materials, high
54057003	900/920	200-900	Ceiling panel with mounting materials, high
54057004	1200/1320	200-900	Ceiling panel with mounting materials, high
54342901	450/460	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
54342902	600/660	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
54342903	900/920	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
54342904	1200/1320	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
54058001	450/460	200-900	Ceiling panel, closed at bottom, with mounting materials
54058002	600/660	200-900	Ceiling panel, closed at bottom, with mounting materials
54058003	900/920	200-900	Ceiling panel, closed at bottom, with mounting materials
54058004	1200/1320	200-900	Ceiling panel, closed at bottom, with mounting materials
540825	up to 300	up to 2100	High cabinet side panel/side wall extension with plinth section
540582	up to 300	up to 2100	High cabinet side panel/side wall extension with top cover and plinth section
540827	up to 300	up to 2100	High cabinet intermediate panel with top cover and plinth section
540864	up to 300	up to 2100	High cabinet corner panel with plinth section without top cover
540828	up to 300	up to 2100	High cabinet corner panel with plinth section with top cover
540591		700-850	Base cabinet corner panel with plinth section, low
540585	up to 300	700-850	Base cabinet side panel/side wall extension with plinth section, low
540829	up to 300	700-850	Base cabinet intermediate panel with plinth section, low
540834	up to 300	600-750	Wall cabinet corner panel, closed at top and bottom, low
540587	up to 300	600-750	Wall cabinet side/intermediate panel, low
54086601		up to 750	Rear wall screen panel for base/top-mounted cabinet
54086602		up to 2000	Rear wall screen panel for high cabinet
54086901		up to 650	Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm
54086902		up to 650	Rear wall (niche panel) between table top and wall cabinet, powder-coated, max. width 2600 mm
543519		100	Plinth end piece

MEGAPROGRESS PANELS AS PER DIN AND ISO STANDARD, STAINLESS STEEL

Panels for cabinets as per DIN and ISO standard, stainless steel


Arr. No. With Height Description Description	Stainless steel			
53056902 600/960 up to 200 Ceiling panel with mounting materials, low 53056903 900/920 up to 200 Ceiling panel with mounting materials, low 53056904 1200 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057901 450/460 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057903 900/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Ceiling panel with mounting materials, high 53057904 1200 up to 200 Ceiling panel with mounting materials, high 53057002 600/960 200-900 Ceiling panel with mounting materials, high 53057003 900/920 200-900 Ceiling panel with mounting materials, high 53057004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials 53058004 1200 up to	Art. No.		•	Description
53056903 900/920 up to 200 Ceiling panel with mounting materials, low 53056904 1200 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057901 450/460 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057902 900/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057903 900/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057001 450/460 200-900 Ceiling panel with mounting materials, high 53057002 600/960 200-900 Ceiling panel with mounting materials, high 53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, high 54353002 800/960 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 1200/930 <th>53056901</th> <th>450/460</th> <th>up to 200</th> <th>Ceiling panel with mounting materials, low</th>	53056901	450/460	up to 200	Ceiling panel with mounting materials, low
53056904 1200 up to 200 Ceiling panel with mounting materials, low 53057901 450/460 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057902 600/660 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057903 300/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057001 450/460 200-900 Ceiling panel with mounting materials, high 53057003 900/920 200-900 Ceiling panel with mounting materials, high 53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1650 mm Ceiling panel with mounting materials, can be cut to size 54353002 600/660 up to 1650 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1650 mm Ceiling panel, closed at bottom, with mounting materials 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 9	53056902	600/660	up to 200	Ceiling panel with mounting materials, low
53057901 450/460 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057902 600/660 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057903 900/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Ceiling panel vidt mounting materials, high 53057001 450/460 200-900 Ceiling panel vidt mounting materials, high 53057003 900/920 200-900 Ceiling panel vidt mounting materials, high 53057001 450/460 200-900 Ceiling panel vidt mounting materials, high 53057003 900/920 200-900 Ceiling panel vidt mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel vidt mounting materials, can be cut to size 54353002 600/660 up to 1050 mm Ceiling panel vidt mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials 53058004 1200 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials 5305803 900/920	53056903	900/920	up to 200	Ceiling panel with mounting materials, low
53057902 600/660 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057903 900/920 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Ceiling panel, closed at bottom, with mounting materials 53057001 450/460 200-900 Ceiling panel with mounting materials, high 53057003 900/920 200-900 Ceiling panel with mounting materials, high 53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel, with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, dosed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, dosed at bottom, with mounting materials 53058003 <t< th=""><th>53056904</th><th>1200</th><th>up to 200</th><th>Ceiling panel with mounting materials, low</th></t<>	53056904	1200	up to 200	Ceiling panel with mounting materials, low
33057903 900/920 up to 200 Coling panel, closed at bottom, with mounting materials 53057904 1200 up to 200 Celling panel, closed at bottom, with mounting materials 53057001 450/460 200-900 Celling panel with mounting materials, high 53057002 600/660 200-900 Celling panel with mounting materials, high 53057004 1200 200-900 Celling panel with mounting materials, high 54353001 450/460 up to 1050 mm Celling panel with mounting materials, can be cut to size 54353002 600/660 up to 1050 mm Celling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Celling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Celling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Celling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Celling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Celling panel, closed at bottom, with mounting materials 53058004 <th>53057901</th> <th>450/460</th> <th>up to 200</th> <th>Ceiling panel, closed at bottom, with mounting materials</th>	53057901	450/460	up to 200	Ceiling panel, closed at bottom, with mounting materials
\$3057904 1200 up to 200 Celling panel, closed at bottom, with mounting materials \$3057001 450/460 200-900 Celling panel with mounting materials, high \$3057002 600/660 200-900 Celling panel with mounting materials, high \$3057003 900/920 200-900 Celling panel with mounting materials, high \$3057004 1200 200-900 Celling panel with mounting materials, can be cut to size \$4353001 450/460 up to 1050 mm Celling panel with mounting materials, can be cut to size \$4353002 600/660 up to 1050 mm Celling panel with mounting materials, can be cut to size \$4353003 900/920 up to 1050 mm Celling panel with mounting materials, can be cut to size \$4353004 1200 200-900 Celling panel, closed at bottom, with mounting materials Can be cut to size \$3058002 600/660 200-900 Celling panel, closed at bottom, with mounting materials Santamerials \$3058003 900/920 200-900 Celling panel, closed at bottom, with mounting materials \$3058004 1200 200-900 Celling panel, closed at bottom, with mounting ma	53057902	600/660	up to 200	Ceiling panel, closed at bottom, with mounting materials
83057001 450/460 200-900 Ceiling panel with mounting materials, high 93057002 600/660 200-900 Ceiling panel with mounting materials, high 93057003 900/920 200-900 Ceiling panel with mounting materials, high 93057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials can be cut to size 54353004 1200 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 5305804 1200 200-900 Ceiling panel, closed at bottom, with mounting materials <t< th=""><th>53057903</th><th>900/920</th><th>up to 200</th><th>Ceiling panel, closed at bottom, with mounting materials</th></t<>	53057903	900/920	up to 200	Ceiling panel, closed at bottom, with mounting materials
53057002 600/660 200-900 Ceiling panel with mounting materials, high 53057003 900/920 200-900 Ceiling panel with mounting materials, high 53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel, closed at bottom, with mounting materials 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530827 <th>53057904</th> <th>1200</th> <th>up to 200</th> <th>Ceiling panel, closed at bottom, with mounting materials</th>	53057904	1200	up to 200	Ceiling panel, closed at bottom, with mounting materials
53057003 900/920 200-900 Ceiling panel with mounting materials, high 53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353002 600/660 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 5305804 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530882 up to 300 up to 2100 High cabinet side panel/side wall extension with top cover	53057001	450/460	200-900	Ceiling panel with mounting materials, high
53057004 1200 200-900 Ceiling panel with mounting materials, high 54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353002 600/660 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530827 up to 300 up to 2100 High cabinet intermediate panel with plinth section with op cover 530828 up to 300 up to 2100 High cabinet corner panel with plinth section with plinth sectio	53057002	600/660	200-900	Ceiling panel with mounting materials, high
54353001 450/460 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353002 600/660 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 53082 up to 300 up to 2100 High cabinet corner panel with plinth section with top cover 53084 up to 300 up to 2100 High cabinet corner panel w	53057003	900/920	200-900	Ceiling panel with mounting materials, high
54353002 600/660 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530682 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530582 up to 300 up to 2100 High cabinet side panel/side wall extension with top cover and plinth section 530827 up to 300 up to 2100 High cabinet intermediate panel with top cover and plinth section 530884 up to 300 up to 2100 High cabinet corner panel with plinth section with top cover 530682 up to 300 up to 2100 High cabinet corner panel with plinth section with top cover 530885 up to 300 700-850 Base cabinet corner panel with plinth section, low 530885 up to 300 700-850 Base cabinet side panel/side wall extension with plinth section, low 530887 up to 300 600-750 Wall cabinet side panel with plinth section, low 530889 up to 300 600-750 Wall cabinet side panel with plinth section, low 530889 up to 300 600-750 Wall cabinet corner panel or base/top-mounted cabinet, max. width 1200 mm 5408604 up to 300 Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm	53057004	1200	200-900	Ceiling panel with mounting materials, high
54353003 900/920 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 5305825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530582 up to 300 up to 2100 High cabinet intermediate panel with pionth section with occover 530847 up to 300 up to 2100 High cabinet corner panel with plinth section without top cover 530888 up to 300 up to 2100 High cabinet corner panel with plinth section, low 530589 up to 300 pon-850 Base cabinet corner panel with plinth section, low 530589 up to 300 700-850 Base cabinet intermediate panel with plinth section, low<	54353001	450/460	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
54353004 1200 up to 1050 mm Ceiling panel with mounting materials, can be cut to size 53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 5305804 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 5305825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530582 up to 300 up to 2100 High cabinet side panel/side wall extension with top cover and plinth section 530847 up to 300 up to 2100 High cabinet intermediate panel with plinth section without top cover 530828 up to 300 up to 2100 High cabinet corner panel with plinth section, low 530591 700-850 Base cabinet corner panel with plinth section, with plinth section, low 530829 up to 300 700-850 Base cabinet side panel/side wall extension with plinth section, low 53084 up to 300 600-750 Wall cabinet side/intermediate panel with	54353002	600/660	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
53058001 450/460 200-900 Ceiling panel, closed at bottom, with mounting materials 53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530582 up to 300 up to 2100 High cabinet side panel/side wall extension with top cover and plinth section 530847 up to 300 up to 2100 High cabinet corner panel with plinth section without top cover 530828 up to 300 up to 2100 High cabinet corner panel with plinth section, low 530591 700-850 Base cabinet corner panel with plinth section, low 530829 up to 300 700-850 Base cabinet intermediate panel with plinth section, low 530847 up to 300 600-750 Wall cabinet corner panel, closed at top and bottom, low 530849 up to 300 600-750 Wall cabinet corner panel, closed at top and bottom, low 5408604 up to 750 Rear wall screen panel for b	54353003	900/920	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
53058002 600/660 200-900 Ceiling panel, closed at bottom, with mounting materials 53058003 900/920 200-900 Ceiling panel, closed at bottom, with mounting materials 53058004 1200 200-900 Ceiling panel, closed at bottom, with mounting materials 530825 up to 300 up to 2100 High cabinet side panel/side wall extension with plinth section 530582 up to 300 up to 2100 High cabinet intermediate panel with top cover and plinth section 530827 up to 300 up to 2100 High cabinet corner panel with plinth section without top cover 530828 up to 300 up to 2100 High cabinet corner panel with plinth section with top cover 530591 700-850 Base cabinet corner panel with plinth section, low 530829 up to 300 700-850 Base cabinet side panel/side wall extension with plinth section, low 530837 up to 300 600-750 Wall cabinet side/intermediate panel, low 53084 up to 300 600-750 Wall cabinet corner panel, closed at top and bottom, low 5308601 up to 500 Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm 54086005 up to 650 Rear wall screen panel for bigh cabinet<	54353004	1200	up to 1050 mm	Ceiling panel with mounting materials, can be cut to size
53058003900/920200-900Ceiling panel, closed at bottom, with mounting materials530580041200200-900Ceiling panel, closed at bottom, with mounting materials530825up to 300up to 2100High cabinet side panel/side wall extension with plinth section530582up to 300up to 2100High cabinet side panel/side wall extension with top cover and plinth section530827up to 300up to 2100High cabinet intermediate panel with top cover and plinth section530848up to 300up to 2100High cabinet corner panel with plinth section without top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530587up to 300700-850Base cabinet intermediate panel with plinth section, low530834up to 300600-750Wall cabinet side/intermediate panel, closed at top and bottom, low5408604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm5408605up to 650Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	53058001	450/460	200-900	Ceiling panel, closed at bottom, with mounting materials
530580041200200-900Ceiling panel, closed at bottom, with mounting materials530825up to 300up to 2100High cabinet side panel/side wall extension with plinth section530582up to 300up to 2100High cabinet side panel/side wall extension with top cover and plinth section530827up to 300up to 2100High cabinet intermediate panel with top cover and plinth section530864up to 300up to 2100High cabinet corner panel with plinth section without top cover530828up to 300up to 2100High cabinet corner panel with plinth section, with top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530887up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low5408604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm5408605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall screen panel for high cabinet	53058002	600/660	200-900	Ceiling panel, closed at bottom, with mounting materials
530825up to 300up to 2100High cabinet side panel/side wall extension with plinth section530582up to 300up to 2100High cabinet side panel/side wall extension with top cover and plinth section530827up to 300up to 2100High cabinet intermediate panel with top cover and plinth section530864up to 300up to 2100High cabinet corner panel with plinth section without top cover530828up to 300up to 2100High cabinet corner panel with plinth section with top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530837up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	53058003	900/920	200-900	Ceiling panel, closed at bottom, with mounting materials
530582up to 300up to 2100High cabinet side panel/side wall extension with top cover and plinth section530827up to 300up to 2100High cabinet intermediate panel with top cover and plinth section530864up to 300up to 2100High cabinet corner panel with plinth section without top cover530828up to 300up to 2100High cabinet corner panel with plinth section with top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	53058004	1200	200-900	Ceiling panel, closed at bottom, with mounting materials
530827up to 300up to 2100High cabinet intermediate panel with top cover and plinth section530864up to 300up to 2100High cabinet corner panel with plinth section without top cover530828up to 300up to 2100High cabinet corner panel with plinth section with top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530825	up to 300	up to 2100	High cabinet side panel/side wall extension with plinth section
530864up to 300up to 2100High cabinet corner panel with plinth section without top cover530828up to 300up to 2100High cabinet corner panel with plinth section with top cover530591700-850Base cabinet corner panel with plinth section, low530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530582	up to 300	up to 2100	High cabinet side panel/side wall extension with top cover and plinth section
530828 up to 300 up to 2100 High cabinet corner panel with plinth section with top cover 530591 700-850 Base cabinet corner panel with plinth section, low 530585 up to 300 700-850 Base cabinet side panel/side wall extension with plinth section, low 530829 up to 300 700-850 Base cabinet intermediate panel with plinth section, low 530587 up to 300 600-750 Wall cabinet side/intermediate panel, low 530834 up to 300 600-750 Wall cabinet corner panel, closed at top and bottom, low 54086604 up to 750 Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm 54086605 up to 2000 Rear wall screen panel for high cabinet 53086901 up to 650 Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530827	up to 300	up to 2100	High cabinet intermediate panel with top cover and plinth section
530591 700-850 Base cabinet corner panel with plinth section, low 530585 up to 300 700-850 Base cabinet side panel/side wall extension with plinth section, low 530829 up to 300 700-850 Base cabinet intermediate panel with plinth section, low 530587 up to 300 600-750 Wall cabinet side/intermediate panel, low 530834 up to 300 600-750 Wall cabinet corner panel, closed at top and bottom, low 54086604 up to 750 Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm 54086605 up to 650 Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530864	up to 300	up to 2100	High cabinet corner panel with plinth section without top cover
530585up to 300700-850Base cabinet side panel/side wall extension with plinth section, low530829up to 300700-850Base cabinet intermediate panel with plinth section, low530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530828	up to 300	up to 2100	High cabinet corner panel with plinth section with top cover
530829up to 300700-850Base cabinet intermediate panel with plinth section, low530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530591		700-850	Base cabinet corner panel with plinth section, low
530587up to 300600-750Wall cabinet side/intermediate panel, low530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530585	up to 300	700-850	Base cabinet side panel/side wall extension with plinth section, low
530834up to 300600-750Wall cabinet corner panel, closed at top and bottom, low54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530829	up to 300	700-850	Base cabinet intermediate panel with plinth section, low
54086604up to 750Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm54086605up to 2000Rear wall screen panel for high cabinet53086901up to 650Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530587	up to 300	600-750	Wall cabinet side/intermediate panel, low
54086605 up to 2000 Rear wall screen panel for high cabinet 53086901 up to 650 Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	530834	up to 300	600-750	Wall cabinet corner panel, closed at top and bottom, low
53086901 up to 650 Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm	54086604		up to 750	Rear wall screen panel for base/top-mounted cabinet, max. width 1200 mm
	54086605		up to 2000	Rear wall screen panel for high cabinet
537939 100 Plinth end piece	53086901		up to 650	Rear wall (niche panel) between table top and wall cabinet, max. width 2600 mm
	537939		100	Plinth end piece

MEGAPROGRESS LADDERS FOR CABINETS AS PER DIN AND ISO STANDARD

Ladder frame for high cabinet with top-mounted cabinet

Ladder frame as attachment for high cabinets, including slide rail


Powder-coated			Stainless steel
Art. No.	Height mm	Description	Art. No.
54321701	100	for hook-in ladder height 100 mm, max. width 2000 mm per frame, first running metre	54321801
54321702	100	for hook-in ladder, height 100 mm, max. width 2000 mm per frame, each further running metre	54321802
54321703	165	for rolling ladder, height 170 mm, max. width 2000 mm per frame, first running metre	54321803
54321704	165	for hook-in ladder, height 170 mm, max. width 2000 mm per frame, each further running metre	54321804



Ladders

Aluminium	
Art. No.	Description
145505	Hook-in ladder, ALU, height 2170 mm, 8 steps
145506	Rolling ladder, ALU, height 2170, 8 steps
543241	Parking position for hook-in ladder, pair

MEGAPROGRESS PANELS AS PER DIN AND ISO STANDARD



Angled top panels for cabinets as per DIN and ISO standard

25 mm at front, 235 mm at rear, up to max. width 1960 mm, for powder-coated steel sheet, up to max. width 1320 mm for

up to max. Width 1900 mm, for powder-coaled steel sheet, up to max. Width 1920 mm
stainless steel in depths: 300 mm, 380 mm, 480 mm, 580 mm, 680 mm

Powder-coate	ed		St. steel
Art. No.	Depth (mm)		Art. No.
54323501	300/380	first running metre	54323701
54323511	300/380	each further running metre up to max. width	54323711
54323502	480/580	first running metre	54323702
54323512	480/580	each further running metre up to max. width	54323712
54323503	680	first running metre	54323703
54323513	680	each further running metre up to max. width	54323713


Cut-out in ceiling panels

Art. No.	Description
602165	Length up to 800 mm

Cut-out in cabinet rear wall including panel

Art. No.

MEGAPROGRESS WALL SHELF




Wall shelf

MWR model

Max. width 2400 mm, surface 240 grain polished Wall shelves, smooth. Turned down 30 mm on all sides Load-bearing capacity with evenly distributed load 75 kg per running metre

Stainless steel		
Art. No.	Depth mm	Description
53639901	300	single-walled, first running metre
53639911	300	single-walled, each further metre up to max. width
53640001	300	double-walled, first running metre
53640011	300	double-walled, each further metre up to max. width
53639902	400	single-walled, first running metre
53639912	400	single-walled, each further metre up to max. width
53640002	400	double-walled, first running metre
53640012	400	double-walled, each further metre up to max. width
53639903	500	single-walled, first running metre
53639913	500	single-walled, each further metre up to max. width
53640003	500	double-walled, first running metre
53640013	500	double-walled, each further metre up to max. width
53639904	600	single-walled, first running metre
53639914	600	single-walled, each further metre up to max. width
53640004	600	double-walled, first running metre
53640014	600	double-walled, each further metre up to max. width




VS wall-mount rails

VS model

Stainless steel		
Art. No.	Description	
53699501	Model VS 0300	
53699502	Model VS 0600	
53699503	Model VS 0900	
53699504	Model VS 1200	
53699505	Model VS 1500	
53699506	Model VS 1800	
53699507	Model VS 2000	

MEGAPROGRESS WALL SHELF



Brackets

KO-V model

for wall-mount rails, height-adjustable

Stainless steel				
Art. No.	Depth mm	Description		
53699601	300	Required number of brackets: Shelf length 1000 mm – 2 pieces Shelf length 1600 mm – 3 pieces Shelf length 2200 mm – 4 pieces		
53699602	400	Required number of brackets: Shelf length 800 mm – 2 pieces Shelf length 1300 mm – 3 pieces Shelf length 1800 mm – 4 pieces Shelf length 2200 mm – 5 pieces		
53699603	500	Required number of brackets: Shelf length 800 mm – 2 pieces Shelf length 1300 mm – 3 pieces Shelf length 1800 mm – 4 pieces Shelf length 2200 mm – 5 pieces		
53699604	600	Required number of brackets: Shelf length 700 mm – 2 pieces Shelf length 1100 mm – 3 pieces Shelf length 1500 mm – 4 pieces Shelf length 1900 mm – 5 pieces Shelf length 2300 mm – 6 pieces		

The FF Co. Ltd.

FF Fémfeldolgozó Co. Ltd. is a medium-sized, family-owned company in Hungary.

For decades we have been specialists in the processing of stainless steel and electrolytically galvanized steel. With our modern machine park, electropolishing facility and powder coating capabilities the main focus of our production program are products for professional commercial kitchens, complete systems for shop-baking equipment, accessories for sterilization equipment and our own "medical line" with furniture for clinics, ambulances and medical practices of the highest quality.

With highly qualified technical staff we are constantly working to improve our products and to implement individual customer requests.

Our head office is located in Budapest, the production site in Mezőtúr.

The product range consists of cabinet systems, functional trolleys, sterile services equipment and mobile furnishings for the operating room.

All of FF Co. Ltd. Professional's divisions have DIN EN ISO 9001:2015, 14001:2015 certification, guaranteeing a high standard of reliability and customer orientation.

Our Partner in

Germany and Western Europe:

MED-Systeme GmbH

http://www.med-systeme.de



All other countries:

FF Co. Ltd. Hungary

http://ffzrt.hu

